



APC Rack PDU, Basic, 1U, 30A, 208V, (10) C13

Brand : APC

Product code: AP9571A

Product name : Rack PDU, Basic, 1U, 30A, 208V, (10) C13



Rack PDU, Basic, 1U, 30A, 208V, (10) C13

APC Rack PDU, Basic, 1U, 30A, 208V, (10) C13:

Reliable rack power distribution designed to increase manageability and efficiency in the data center The output and input connections are (10) C13 Real-time remote monitoring of connected loads User-defined alarms warn IT and data center managers of potential circuit overloads to prevent accidental power loss to critical equipment.

APC Rack PDU, Basic, 1U, 30A, 208V, (10) C13. Product colour: Grey. Input connection type: NEMA L6-30P. Cable length: 3.66 m. AC input frequency: 60 Hz, Nominal output voltage: 208 V, Maximum total current draw per phase: 24 A. Width: 445 mm, Depth: 77 mm, Height: 44 mm

Design		Operational conditions	
Product colour	Grey	Storage temperature (T-T)	-25 - 65 °C
Ports & interfaces		Operating relative humidity (H-H)	5 - 95%
Input connection type	NEMA L6-30P	Storage relative humidity (H-H)	5 - 95%
Features		Weight & dimensions	
Cable length	3.66 m	Width	445 mm
Power		Depth	77 mm
AC input frequency	60 Hz	Height	44 mm
Nominal output voltage	208 V	Weight	2.55 kg
Maximum total current draw per phase	24 A	Logistics data	
Operational conditions		Total carbon footprint (kg of CO2e)	65.42
Operating temperature (T-T)	-15 - 45 °C		



0731304272755



731304272755

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.