



APC 5kVA and 6kVA Marine Filter Rack-Mount

Brand : APC

Product code: SRT6RMM

Product name : 5kVA and 6kVA Marine Filter Rack-Mount



5kVA and 6kVA Marine Filter Rack-Mount


APC 5kVA and 6kVA Marine Filter Rack-Mount:

High availability, ruggedized power protection for shipboard and other transportation applications. APC 5kVA and 6kVA Marine Filter Rack-Mount. Output power capacity: 6 kVA, Input operation voltage (min): 100 V, Input operation voltage (max): 240 V. AC outlet types: Hardwire. Form factor: Rackmount, Product colour: Black, Rack capacity: 1U. Width: 483 mm, Depth: 330 mm, Height: 44 mm. Package width: 559 mm, Package depth: 406 mm, Package height: 76 mm


Features		Operational conditions	
Output power capacity *	6 kVA	Operating temperature (T-T)	0 - 55 °C
Input operation voltage (min) *	100 V	Storage temperature (T-T)	-25 - 75 °C
Input operation voltage (max) *	240 V	Operating relative humidity (H-H)	0 - 95%
Input frequency *	45/65 Hz	Storage relative humidity (H-H)	0 - 95%
Output operation voltage (min)	200 V	Weight & dimensions	
Output operation voltage (max)	240 V	Width	483 mm
Ports & interfaces		Depth	330 mm
AC outlet types	Hardwire	Height	44 mm
Design		Weight	6.73 kg
Form factor *	Rackmount	Packaging data	
Rack capacity	1U	Package width	559 mm
Product colour *	Black	Package depth	406 mm
		Package height	76 mm
		Package weight	8.27 kg
		Logistics data	
		Harmonized System (HS) code	85078000



0731304324843



731304324843



5054444430225



8592978445324

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.