



APC NetShelter SX 42U Freestanding rack Black

Brand : APC
Product code: AR3300
Product name : NetShelter SX 42U

NetShelter SX 42U 600mm Wide x 1200mm Deep Enclosure

APC NetShelter SX 42U Freestanding rack Black:

Rack enclosures with advanced cooling, power distribution, and cable management for server and networking applications in IT environments.

Includes: Baying hardware, Documentation CD, Key(s), Leveling feet, Mounting Hardware, Pre-installed casters, Side Panels, User Manual.
APC NetShelter SX 42U. Type: Freestanding rack, Rack capacity: 42U, Maximum weight capacity: 1704 kg. Weight: 134.1 kg. Product colour: Black



Features		Packaging data	
Rack capacity *	42U	Package weight	149.1 kg
Type *	Freestanding rack	Technical details	
Maximum weight capacity *	1704 kg	Total carbon footprint (kg of CO2e)	452.38
Product colour	Black	Logistics data	
Weight & dimensions		Harmonized System (HS) code	85381000
Size (imperial)	48.3 cm (19")	Other features	
Width	600 mm	Dimensions (WxDxH)	600 x 1200 x 1991 mm
Depth	1200 mm	Package dimensions (WxDxH)	746 x 1334 x 2118 mm
Height	1991 mm	Dynamic load	1022.73 kg
Weight	134.1 kg	Static load	1363.64 kg
Mounting depth (min)	19.1 cm		
Mounting depth (max)	104.8 cm		



0731304256274



731304256274

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.