



APC 3.5kW split system Outdoor unit, None pre-charged refrigerant

Brand : APC

Product code: ACRMD4KI-3

Product name : 3.5kW split system Outdoor unit, None pre-charged refrigerant

- Powerfully Compact- precise temperature control to cool most single racks with zero need for alternative solutions
 - Enhanced Flexibility-Installs and integrates quickly and simply at the bottom of the IT Rack
 - Variable Capacity- continuous and automatic modulation of fan and compressor speed to match rack airflow requirements
 - Robust Design- for 24/7 continuous operation and convenient servicing of critical components outside the IT space
- 3.5kW split system Outdoor unit, None pre-charged refrigerant

APC 3.5kW split system Outdoor unit, None pre-charged refrigerant:

This product ACRMD4KI-3 is a compact, intelligent cooling for your Edge Data Center.



Features		Power	
Type *	Air conditioner outdoor unit	Design load (heating) (Colder heating season)	3.5 kW
Multi-split *	✗		
Product colour *	White		
Air conditioner functions *	Circulation, Cooling, Heating		
Inverter technology *	✗		
Ionizer *	✗		
Power		Network	
Design load (heating) (Warmer heating season) *	3.5 kW	Wi-Fi *	✗
Design load (heating) (Average heating season) *	3.5 kW		
		Indoor unit	
		Indoor unit width	85.6 cm
		Indoor unit depth	29.6 cm
		Indoor unit height	61.7 cm
		Indoor unit weight	44.4 kg
		Outdoor unit	
		Outdoor unit noise level	51.5 dB



0731304403807



731304403807

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.