

Epson SureColor SC-P900 photo printer 5760 x 1440 DPI 8" x 10" (20x25 cm) Wi-Fi



Brand : Epson

Product family: SureColor

Product code: C11CH37401DA

Product name : SC-P900

- Epson Micro Piezo print head
- 4.3-inch LCD optical touchscreen
- Black enhance overcoat technology for finer detail and texture
- Easily handles different media types
- Epson Connect (iPrint), Apple AirPrint, Google Cloud Print
- USB 3.0, Wi-Fi 802.11a/b/g/n/ac, Wi-Fi Direct

Epson Micro Piezo print head, 5760 x 1440 DPI printing resolution, Manual duplex, Mobile and cloud printing services, LCD optical touchscreen, USB 3.0, Wi-Fi

Epson SureColor SC-P900. Maximum resolution: 5760 x 1440 DPI. Maximum print size: 8" x 10" (20x25 cm). Borderless printing, Duplex printing. Wi-Fi. Product colour: Black

Printing		Network	
Borderless printing *	✓	Wi-Fi *	✓
Duplex printing	✓	Mobile printing technologies	Apple AirPrint, Epson Connect, Google Cloud Print
Duplex printing mode	Manual		
Maximum resolution *	5760 x 1440 DPI		
Features		Performance	
Market positioning *	Professional	Sound pressure level (printing)	41 dB
Product colour *	Black	Power	
Colour name	Black	Power source *	AC
Number of print cartridges	1	Power consumption (printing) *	24 W
Printing colours	Cyan, Grey, Light Cyan, Light grey, Matte black, Photo black, Violet, Vivid light magenta, Vivid magenta, Yellow	Power consumption (standby)	1.1 W
Built-in display	✓	Power consumption (off)	0.18 W
Display	LCD	AC input voltage	100 - 240 V
Display diagonal	10.9 cm (4.3")	AC input frequency	50 - 60 Hz
Control type	Touch	System requirements	
Input & output capacity		Windows operating systems supported	Windows 10, Windows 7, Windows 8, Windows 8.1
Total input capacity	120 sheets	Mac operating systems supported	Mac OS X 10.10 Yosemite, Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, Mac OS X 10.15 Catalina, Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
Paper handling		Weight & dimensions	
Maximum print size *	8" x 10" (20x25 cm)	Width	615 mm
Paper tray media types	Postcard	Depth	368 mm
Maximum ISO A-series paper size	A2	Height	199 mm
ISO A-series sizes (A0...A9)	A2, A3, A3+, A4, A5	Weight	14.8 kg
Non-ISO print media sizes	Legal, Letter	Packaging data	
Printing sizes	10 x 15, 13 x 18, 13 x 20, 20 x 25	AC adapter included	✓
Ports & interfaces		Logistics data	
USB port *	✓	Harmonized System (HS) code	84433210



8715946686561

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.