



Origin Storage 85552 InfiniBand/fibre optic cable 5 m LC OFNR Aqua colour

Brand : Origin Storage

Product code: 85552

Product name : 85552



LC-LC 10Gb 50/125 OM3 Duplex Multimode PVC Fibre Optic Cable

Origin Storage 85552 InfiniBand/fibre optic cable 5 m LC OFNR Aqua colour:

This OM3 Duplex Multimode Fibre Optic Cable is ideal for connecting 10GBase-SR, 10GBase-LRM, SFP+ and QSFP+ transceivers for 10 gigabit network connections. This cable has a LSZH jacket which protects from toxic and corrosive gases in poorly ventilated spaces and other areas where it is most critical. This cable also provides backward compatibility with existing 50/125 equipment and the performance headroom required to support LED and VCSEL laser light sources, and 10 Gigabit Ethernet applications. Origin Storage 85552. Cable length: 5 m, Cable type: OFNR, Fibre optic type: OM3, Connector 1: LC, Connector 2: LC, Core diameter: 50 µm, Full duplex

Features		Features	
Cable length *	5 m	Product colour *	Aqua colour
Fibre optic type	OM3	Full duplex	✓
Connector 1 *	LC	Core diameter	50 µm
Connector 2 *	LC	Cladding diameter	125 µm
Connector 1 gender *	Male	Fiber mode structure	Multi-mode
Connector 2 gender *	Male	Jacket material *	Polyvinyl chloride (PVC)
Cable type *	OFNR	Operational conditions	
		Operating temperature (T-T)	-20 - 70 °C



075712085521



75712085521

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.