Lenovo 4X90R61022 video cable adapter 0.24 m USB Type-C HDMI Type A (Standard) Black

Brand : Lenovo

Product code: 4X90R61022

Product name : 4X90R61022

USB C - HDMI, M/F, 0.24 m, Black

Lenovo 4X90R61022 video cable adapter 0.24 m USB Type-C HDMI Type A (Standard) Black:

The Lenovo USB-C to HDMI 2.0b Adapter connects USB-C enabled notebooks to HDMI enabled displays such as monitors and projectors. Its 240mm (9.4") length and 34g (0.07lbs) weight make it versatile and travel ready. So you can enjoy all the benefits of HDMI 2.0b technology, like support for resolutions up to UHD 4K @60Hz, at any time.
Lenovo 4X90R61022. Cable length: 0.24 m, Connector 1: USB Type-C, Connector 2: HDMI Type A (Standard). Weight: 34 g. Quantity per pack: 1 pc(s)

Features	
Connector 1 form factor	Straight
Connector 2 form factor	Straight
Cable length *	0.24 m
Connector 1 *	USB Type-C
Connector 2 *	HDMI Type A (Standard)
Connector 1 gender *	Male
Connector 2 gender *	Male
HDMI version	2.0b

Features	
Maximum resolution	3840 x 2160 pixels
Product colour	Black
Plug and Play	✔
Weight & dimensions	
Weight	34 g
Packaging content	
Quantity per pack	1 pc(s)
Logistics data	
Harmonized System (HS) code	84733080



0192940376274



192940376274



4589702035467

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date