



APC Easy Rack, 48U, Black, With Roof, Castors, Feet, 4 Brackets, and Bottom, No Side Panels, 2258H x 600W x 1200D mm



Brand : APC

Product code: ER6820


Product name : Easy Rack, 48U, Black, With Roof, Castors, Feet, 4 Brackets, and Bottom, No Side Panels, 2258H x 600W x 1200D mm

Easy Rack, 48U, Black, With Roof, Castors, Feet, 4 Brackets, and Bottom, No Side Panels, 2258H x 600W x 1200D mm

APC Easy Rack, 48U, Black, With Roof, Castors, Feet, 4 Brackets, and Bottom, No Side Panels, 2258H x 600W x 1200D mm. Type: Freestanding rack, Rack capacity: 48U, Maximum weight capacity: 1199.75 kg, Castor wheels. Weight: 90 kg. Product colour: Black



Features		Weight & dimensions	
Rack capacity *	48U	Height	2258 mm
Type *	Freestanding rack	Weight	90 kg
Maximum weight capacity *	1199.75 kg	Packaging data	
Maximum weight capacity (rolling)	599.65 kg	Package width	650 mm
Product colour	Black	Package depth	1250 mm
Side panels included	✗	Package height	2390 mm
Castor wheels	✓	Package weight	98 kg
Weight & dimensions		Technical details	
Width	600 mm	Total carbon footprint (kg of CO2e)	297.36
Depth	1200 mm	Logistics data	
		Harmonized System (HS) code	85381000



0731304433293



731304433293

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.