



QNAP QSW-M804-4C network switch Managed 10G Ethernet (100/1000/10000) Black

Brand : QNAP

Product code: QSW-M804-4C

Product name : QSW-M804-4C

8x 10GbE SFP+/RJ45, 4x 10GbE SFP+, 160Gbps, 46.65 x 285 x 236.6 mm

QNAP QSW-M804-4C. Switch type: Managed. Basic switching RJ-45 Ethernet ports type: 10G Ethernet (100/1000/10000), Console port: RS-232. Full duplex. MAC address table: 16000 entries, Switching capacity: 160 Gbit/s. Networking standards: IEEE 802.1Q, IEEE 802.1ab, IEEE 802.1p, IEEE 802.1w, IEEE 802.3, IEEE 802.3ab, IEEE 802.3ad, IEEE.... Rack mounting



Management features		Performance	
Switch type *	Managed	Firmware upgradeable	✓
Quality of Service (QoS) support	✓	Power	
Web-based management	✓	Power source *	AC
Ports & interfaces		Power supply included *	✓
Basic switching RJ-45 Ethernet ports type *	10G Ethernet (100/1000/10000)	AC input voltage	100 - 240 V
Combo SFP ports quantity	4	AC input frequency	50 - 60 Hz
SFP+ module slots quantity	4	Power consumption (max)	70 W
Console port	RS-232	Power over Ethernet (PoE)	
Network		Power over Ethernet (PoE) *	✗
Networking standards *	IEEE 802.1Q, IEEE 802.1ab, IEEE 802.1p, IEEE 802.1w, IEEE 802.3, IEEE 802.3ab, IEEE 802.3ad, IEEE 802.3ae, IEEE 802.3an, IEEE 802.3az, IEEE 802.3bz, IEEE 802.3u, IEEE 802.3x, IEEE 802.3z	Other features	
		Warranty period	2 year(s)
10G support *	✓	Operational conditions	
Full duplex	✓	Operating temperature (T-T)	0 - 40 °C
Flow control support	✓	Operating relative humidity (H-H)	5 - 95%
Spanning tree protocol	✓	Weight & dimensions	
Auto-negotiation	✓	Width	285 mm
VLAN support	✓	Depth	233 mm
Virtual LAN features	Port-based VLAN	Height	43 mm
Data transmission		Weight	2.12 kg
Switching capacity *	160 Gbit/s	Packaging content	
Throughput	80 Gbit/s	Cables included	AC
MAC address table *	16000 entries	User guide	✓
Jumbo frames support	✓	Packaging data	
Jumbo frames	9000	Package type	Box
Security		Package width	384 mm
DHCP features	DHCP client	Package depth	282 mm
Access Control List (ACL)	✓	Package height	78 mm
IGMP snooping	✓	Package weight	2.94 kg
		Certificates	
		Certification	FCC, CE, VCCI, BSMI, RCM, WEEE
		Logistics data	

Design		Logistics data	
Rack mounting *	✓	Country of origin	Taiwan
Product colour	Black	Harmonized System (HS) code	85176990
Reset button	✓	Products per master (outer) case	5 pc(s)
LED indicators	Activity, Link, Power, Speed, Status		
Number of fans	4 fan(s)		
Electromagnetic compatibility	CLASS A		



4713213517819



0885022019830



885022019830

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.