



APC Protocol translation to UPS-Link, Management Options, Legacy Communications SmartSlot Card, UPS support for UPSLink protocol serial communications

Brand : APC

Product code: AP9620

Product name : Protocol translation to UPS-Link, Management Options, Legacy Communications SmartSlot Card, UPS support for UPSLink protocol serial communications

Protocol translation to UPS-Link, Management Options, Legacy Communications SmartSlot Card, UPS support for UPSLink protocol serial communications


APC Protocol translation to UPS-Link, Management Options, Legacy Communications SmartSlot Card, UPS support for UPSLink protocol serial communications:

The Legacy Communications SmartSlot Card provides serial communications support for the UPS-Link protocol for SC, SMC, SMX, SMT, SURTD, SRT UPS models. These UPS devices no longer communicate using the UPS-Link protocol. The Legacy Communications Card can be used for custom applications using the UPS-Link protocol.

APC Protocol translation to UPS-Link, Management Options, Legacy Communications SmartSlot Card, UPS support for UPSLink protocol serial communications. Certification: RoHS. Width: 121 mm, Depth: 114 mm, Height: 38 mm. Package weight: 340 g. Connectivity technology: Wired, Package dimensions (WxDxH): 235 x 159 x 51 mm



Ports & interfaces		Technical details	
USB 2.0 ports quantity	1	Total carbon footprint (kg of CO2e)	109.58
Serial ports quantity	1	Weight & dimensions	
Design		Width	121 mm
Certification	RoHS	Depth	114 mm
Operational conditions		Height	38 mm
Operating temperature (T-T)	0 - 45 °C	Weight	80 g
Storage temperature (T-T)	-5 - 45 °C	Packaging data	
Operating relative humidity (H-H)	0 - 95%	Package weight	340 g
Storage relative humidity (H-H)	0 - 95%	Logistics data	
		Harmonized System (HS) code	84733020
		Other features	
		Connectivity technology	Wired
		Package dimensions (WxDxH)	235 x 159 x 51 mm



0731304283218



731304283218

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.