



Lenovo ThinkPad Thunderbolt 3 Workstation Gen 2 Wired Black



Brand : Lenovo

Product code: 40ANY230UK

Product name : ThinkPad Thunderbolt 3 Workstation Gen 2

5x USB 3.0, Thunderbolt 3, 2x DisplayPort, 2x HDMI, 1x Ethernet, 525g

[Lenovo ThinkPad Thunderbolt 3 Workstation Gen 2 Wired Black:](#)

The ThinkPad Thunderbolt 3 Workstation Dock Gen 2 (40AN) turns your ThinkPad Mobile Workstation into a productivity powerhouse, adding support for multi 4K displays, optimized one cable charging, a slew of expansion ports, and advanced network manageability features.

Lenovo ThinkPad Thunderbolt 3 Workstation Gen 2. Connectivity technology: Wired, Host interface: Thunderbolt 3. Ethernet LAN data rates: 10,100,1000 Mbit/s. Product colour: Black, Maximum digital resolution: 3840 x 2160 pixels, Brand compatibility: Lenovo. Windows operating systems supported: Windows 10. Width: 220 mm, Depth: 80 mm, Height: 30 mm

Ports & interfaces		Software	
Connectivity technology *	Wired	Windows operating systems supported	Windows 10
Host interface *	Thunderbolt 3	Operational conditions	
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity *	5	Operating temperature (T-T)	0 - 40 °C
HDMI ports quantity *	2	Operating relative humidity (H-H)	5 - 95%
DisplayPorts quantity	2	Weight & dimensions	
Microphone in *	✗	Width	220 mm
Combo headphone/mic port	✓	Depth	80 mm
DC-in jack	✓	Height	30 mm
Network		Weight	525 g
Ethernet LAN *	✓	Packaging data	
Ethernet LAN (RJ-45) ports	1	Quantity per pack	1 pc(s)
Ethernet LAN data rates	10,100,1000 Mbit/s	Package width	270 mm
Performance		Package depth	195 mm
Card reader integrated *	✗	Package height	85 mm
Maximum digital resolution	3840 x 2160 pixels	Package weight	1.9 kg
Product colour *	Black	Packaging content	
Brand compatibility	Lenovo	Cables included	AC, Thunderbolt
Compatibility	ThinkPad L390 (20NR, 20NS), ThinkPad L390 Yoga (20NT, 20NU), Thinkpad L490 (20Q5,20Q6), Thinkpad L590 (20N7,20N8), Thinkpad E590 20NB, 20NC), Thinkpad E490 (20N8, 20N9), Thinkpad E490s (20NG)	AC adapter included	✓
		Quick start guide	✓
		User guide	✓
		Logistics data	
Certification	CE-EMC, TUV Mark,KCC,Serbia Kvalitet, CU EAC	Harmonized System (HS) code	84733020
Audio			
Built-in speaker(s)	✗		



0193638285953



193638285953

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.