



HyperX Pulsefire Core - Gaming Mouse (Black)

Brand : HyperX

Product family: HyperX

Product code: 4P4F8AA

Product name : HyperX
Pulsefire Core - Gaming Mouse
(Black)

HyperX Pulsefire Core - Gaming Mouse (Black)


HyperX Pulsefire Core - Gaming Mouse (Black):

Solid gaming-grade optical mouse with customizable RGB lighting

The HyperX Pulsefire Core™ delivers the essentials for gamers looking for a solid, comfortable, wired RGB gaming mouse. The Pixart 3327 optical sensor gives players precise, smooth tracking with no hardware acceleration, and has native DPI settings up to 6200 DPI. The ergonomically-designed Pulsefire Core has textured side grips for a comfortable, no-slip grip, and its symmetrical shape is suitable for both palm and claw grip. It features high-quality switches with crisp tactile feedback rated for up to 20 million clicks. Customize lighting, DPI settings, and macros for 7 programmable buttons with HyperX NGENUITY software and set your mouse up just the way you want it. The large skates on Pulsefire Core help deliver accurate aiming by giving you a smooth, controlled glide as you move the mouse.



Mouse		Weight & dimensions	
Purpose *	Gaming	Depth	64 mm
Movement detection technology *	Optical	Height	41 mm
Movement resolution *	6200 DPI	Weight	87 g
Scroll type *	Wheel	Packaging data	
Buttons quantity *	7	AC adapter included *	✗
Mouse tracking speed	220 ips	Package width	119 mm
Acceleration (max)	30 G	Package depth	59 mm
Polling rate	1000 Hz	Package height	179 mm
Design		Package weight	200 g
Form factor *	Ambidextrous	Sustainability	
Product colour *	Black	Total carbon footprint (kg of CO2e)	
Colour name	Black	10	
Ergonomics		Technical details	
Cable length	1.8 m	General Product Safety Regulation (GPSR) URL	https://kaas.hpcloud.hp.com/pdf-public/pdf_8666243_en-US-1.pdf https://row.hyperx.com/pages/limited-warranty-statement
Power		Other features	
Power source *	Cable	Compatibility	PC, PS5™, PS4™, Xbox Series X S™, and Xbox One™. Software Compatibility: HyperX NGENUITY
USB Type-C charging port *	✗	UNSPSC-code	43211708
USB Power Delivery (USB PD)	✗	Logistics data	
Weight & dimensions		Country of origin	China
Width	119 mm	Harmonized System (HS) code	84716070



0196188043127



196188043127



7406172790788

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.