



APC Easy UPS On-Line SRV 36V RM Battery Pack for 1 kVA
Extended Runtime Model

Brand : APC

Product code: SRV36RLBP-9A

Product name : APC Easy UPS On-Line SRV 36V RM
Battery Pack for 1 kVA Extended Runtime Model




- High quality, Double-conversion On-line UPS designed for essential power protection needs even in the most unstable power conditions
- Includes: Documentation CD, User Manual

APC Easy UPS On-Line SRV 36V RM Battery Pack for 1 kVA Extended Runtime Model
APC Easy UPS On-Line SRV 36V RM Battery Pack for 1 kVA Extended Runtime Model. Battery technology: Sealed Lead Acid (VRLA), Battery voltage: 36 V, Number of batteries included: 1 pc(s). Compliance certificates: RoHS, Certification: REACH. Weight: 21 kg, Width: 438 mm, Height: 86 mm. Package width: 500 mm, Package height: 240 mm, Package depth: 600 mm



Features		Packaging data	
Battery technology *	Sealed Lead Acid (VRLA)	Package width	500 mm
Battery voltage *	36 V	Package height	240 mm
Number of batteries included *	1 pc(s)	Package depth	600 mm
Product colour	Black	Package weight	24.2 kg
Certificates		Operational conditions	
Compliance certificates	RoHS	Storage temperature (T-T)	-15 - 40 °C
Certification	REACH	Operating relative humidity (H-H)	0 - 95%
Weight & dimensions		Storage relative humidity (H-H)	0 - 95%
		Logistics data	
		Harmonized System (HS) code	85044095
		Total carbon footprint (kg of CO2e)	110.81



0731304403050



731304403050

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.