ZYXEL

Zyxel WAX630S 2400 Mbit/s White Power over Ethernet (PoE)

Brand : Zyxel

Product code: WAX630S-EU0101F

Product name : WAX630S



WAX630S, Single Pack 802.11ax 4x4 Smart Antenna exclude Power Adaptor
Zyxel WAX630S. 2.4 GHz, 5 GHz, Maximum data transfer rate: 2400 Mbit/s. Security algorithms: EAP, WEP, WPA, WPA2-PSK, WPA3, WPA3-Enterprise. Ethernet LAN data rates: 1000,2500 Mbit/s. Power over Ethernet (PoE). Product colour: White



Features	
2.4 GHz *	✔
5 GHz *	✔
Maximum data transfer rate *	2400 Mbit/s
Maximum data transfer rate (2.4 GHz)	575 Mbit/s
Maximum data transfer rate (5 GHz)	2400 Mbit/s
Ethernet LAN data rates	1000,2500 Mbit/s
Networking standards	IEEE 802.11a, IEEE 802.11ac, IEEE 802.11ax, IEEE 802.11b, IEEE 802.11g, IEEE 802.11k, IEEE 802.11n, IEEE 802.11r, IEEE 802.11v, IEEE 802.3at
MIMO	✔
MIMO type	Multi User MIMO
VLAN support	✔
Security	
Security algorithms *	EAP, WEP, WPA, WPA2-PSK, WPA3, WPA3-Enterprise
MAC address filtering	✔
Management features	
Web-based management	✔
Ports & interfaces	
Ethernet LAN (RJ-45) ports *	2

Ports & interfaces	
DC-in jack	✔
Power	
Power over Ethernet (PoE) *	✔
Output voltage	12 V
Output current	2 A
Design	
Product colour *	White
LED indicators	✔
Antenna	
Antenna type *	Internal
Weight & dimensions	
Width	180 mm
Depth	180 mm
Height	39 mm
Weight	530 g
Packaging content	
Quantity per pack	1 pc(s)
Mounting kit	✔
Logistics data	
Harmonized System (HS) code	85176990

4718937619474

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date