



Lenovo 4P57A26291 power supply unit 750 W Flex ATX Silver

Brand : Lenovo
Product code: 4P57A26291
Product name : 4P57A26291



ThinkSystem 750W (230/115V) v2 Platinum Hot-Swap Power Supply


Lenovo 4P57A26291 power supply unit 750 W Flex ATX Silver:

Dual-voltage power supplies are auto-sensing and support both 110V AC (100-127V 50/60 Hz) and 220V AC (200-240V 50/60 Hz) power. For China customers, all power supplies support 240V DC.

All supported AC power supplies have a C14 connector. The -48V DC power supply has a Weidmuller TOP 4GS/3 7.6 terminal as shown in the following figure.

Lenovo 4P57A26291. Total power: 750 W, AC input voltage: 115 - 230 V, AC input frequency: 50 - 60 Hz. Connector(s): C14. Purpose: Server, Power supply unit (PSU) form factor: Flex ATX, 80 PLUS certification: 80 PLUS Platinum. Product colour: Silver, Cooling type: Active, Fan location: Front. Package type: Box

Power		Performance	
Total power *	750 W	Power supply unit (PSU) form factor *	Flex ATX
AC input voltage *	115 - 230 V	Compatible products	ThinkSystem
AC input frequency	50 - 60 Hz		
Ports & interfaces		Design	
Connector(s)	C14	Product colour	Silver
Performance	80 PLUS Platinum	Cooling type	Active
		Fan location	Front
80 PLUS certification *	80 PLUS Platinum	Packaging data	
Purpose *	Server	Package type	Box
		Logistics data	
		Harmonized System (HS) code	84733020



0889488525188



889488525188

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.