




Lenovo 4C57A14177 interface cards/adapter Internal InfiniBand, QSFP56

Brand : Lenovo
Product code: 4C57A14177
Product name : 4C57A14177




ThinkSystem Mellanox ConnectX-6 HDR100/100GbE QSFP56 1-port PCIe VPI Adapter

Lenovo 4C57A14177 interface cards/adapter Internal InfiniBand, QSFP56:

The ThinkSystem Mellanox ConnectX-6 HDR100/100GbE VPI Adapters offer 100 Gb/s Ethernet and InfiniBand connectivity for high-performance connectivity when running HPC, cloud, storage and machine learning applications.
Lenovo 4C57A14177. Host interface: PCIe, Output interface: InfiniBand, QSFP56. Product colour: Multicolour, Purpose: Server, Cooling type: Passive

Ports & interfaces		Design	
Host interface *	PCIe	Number of expansion slots	1
Output interface *	InfiniBand, QSFP56	Certification	Safety: CB / cTUVus / CE EMC: CE / FCC / VCCI / ICES / RCM / KC RoHS: RoHS Compliant
Design		Operational conditions	
Internal *	✓	Operating temperature (T-T)	0 - 55 °C
Product colour	Multicolour	Storage temperature (T-T)	-40 - 70 °C
Purpose	Server	Operating relative humidity (H-H)	0 - 90%
Cooling type	Passive		



0889488476381



889488476381

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.