



APC NetShelter SX 48U Freestanding rack Black

Brand : APC
Product code: AR3107SP
Product name : NetShelter SX 48U

48U, 600mm (W) x 1070mm (D), Black, Shock Packaging

APC NetShelter SX 48U Freestanding rack Black:

Tall enclosure with 48U spaces for additional equipment. Compact width to optimize data center space. For low to medium density server and networking applications.


Includes: Baying hardware, Documentation CD, Key(s), Keyed-alike doors and side panels, Leveling feet, Mounting Hardware, Pre-installed casters, Side Panels.
APC NetShelter SX 48U. Type: Freestanding rack, Rack capacity: 48U, Maximum weight capacity: 1704 kg, Key lock. Weight: 138.2 kg. Product colour: Black



Features		Weight & dimensions	
Rack capacity *	48U	Depth	1070 mm
Type *	Freestanding rack	Height	2258 mm
Maximum weight capacity *	1704 kg	Weight	138.2 kg
Product colour	Black	Packaging data	
Material	Metal	Package width	1105 mm
Key lock	✓	Package depth	1320.8 mm
Certification	UL 60950 RoHS REACH PEP EOLi	Package height	2450 mm
Weight & dimensions		Package weight	240.9 kg
Size (imperial)	48.3 cm (19")	Logistics data	
Width	600 mm	Harmonized System (HS) code	85381000



0731304309871



731304309871

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.