APC Battery Replacement Cartridge APCRBC135 (OEM)



Brand : APC

Product code: APCRBC135

Product name : Battery Replacement Cartridge APCRBC135 (OEM)

Battery Replacement Cartridge APCRBC135 (OEM)

APC Battery Replacement Cartridge APCRBC135 (OEM):

APC Replacement Battery Cartridge #135

Genuine APC RBC are tested and certified for compatibility to restore UPS performance to the original specifications.
APC Battery Replacement Cartridge APCRBC135 (OEM). Battery technology: Sealed Lead Acid (VRLA), Battery capacity: 168 VAh, Battery life: 5 year(s). Compliance certificates: RoHS, Certification: REACH. Weight: 4.68 kg, Width: 107 mm, Height: 107 mm. Package width: 229 mm, Package height: 229 mm, Package depth: 229 mm

Features	
Battery technology *	Sealed Lead Acid (VRLA)
Battery capacity	168 VAh
Battery life	5 year(s)
Product colour	Black
Hot-swap battery	✔

Certificates	
Compliance certificates	RoHS
Certification	REACH

Weight & dimensions	
Weight	4.68 kg
Width	107 mm
Height	107 mm
Depth	144 mm

Packaging data	
Package width	229 mm
Package height	229 mm
Package depth	229 mm
Package weight	5.14 kg

Operational conditions	
Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	-15 - 45 °C
Operating relative humidity (H-H)	0 - 95%
Operating altitude	0 - 3000 m
Non-operating altitude	0 - 15000 m

Logistics data	
Harmonized System (HS) code	85044095

0731304291732

731304291732

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date