


StarTech.com 18in Latching SATA to Right Angle SATA Serial ATA Cable

Brand : StarTech.com

Product code: LSATA18RA1

Product name : 18in Latching SATA to Right Angle SATA Serial ATA Cable

StarTech.com 18in Latching SATA to Right Angle SATA Serial ATA Cable
StarTech.com 18in Latching SATA to Right Angle SATA Serial ATA Cable. Cable length: 0.457 m, Cable type: SATA III, Connector 1: SATA 7-pin. Compliance certificates: CE, RoHS. Quantity per pack: 1 pc(s), Package width: 125 mm, Package depth: 255 mm. Master (outer) case width: 334 mm, Master (outer) case length: 486 mm, Master (outer) case height: 216 mm



Features		Certificates	
Cable length *	0.457 m	Compliance certificates	CE, RoHS
Cable type *	SATA III	Packaging data	
Connector 1 *	SATA 7-pin	Quantity per pack	1 pc(s)
Connector 2 *	SATA 7-pin	Package width	125 mm
Connector 1 form factor	Straight	Package depth	255 mm
Connector 2 form factor	Right	Package height	18 mm
Connector gender *	Male/Male	Package weight	84 g
Product colour *	Red	Logistics data	
Maximum data transfer rate	6 Gbit/s	Master (outer) case width	334 mm
Sustainability		Master (outer) case length	486 mm
Sustainability compliance	✓	Master (outer) case height	216 mm
		Products per master (outer) case	200 pc(s)



0065030818889



065030818889

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.