

ASUS Chromebox CHROMEBOX5-S7009UN+ Intel® Core™ i7 i7-1260P 16 GB DDR4-SDRAM 256 GB SSD ChromeOS Mini PC Black

Brand : ASUS

Product family: Chromebox

Product code: 90MS02N1-M001E0

Product name :
CHROMEBOX5-S7009UN+

- ChromeOS

- Intel Core i7-1260P (18MB Cache)

- 16GB (3200MHz) DDR4-SDRAM & 256GB SSD

Intel Core i7-1260P (18MB Cache), 16GB DDR4-SDRAM, 256GB SSD, Intel Iris Xe Graphics, LAN, WLAN, Bluetooth, ChromeOS

ASUS Chromebox CHROMEBOX5-S7009UN+. Processor family: Intel® Core™ i7, Processor model: i7-1260P. Internal memory: 16 GB, Internal memory type: DDR4-SDRAM, Memory clock speed: 3200 MHz. Total storage capacity: 256 GB, Storage media: SSD, Card reader integrated. On-board graphics card model: Intel Iris Xe Graphics. Operating system installed: ChromeOS. Power supply: 150 W. Chassis type: Mini PC. Product type: Mini PC. Weight: 800 g. Product colour: Black



Processor		Network	
Processor manufacturer *	Intel	Bluetooth	✓
Processor family *	Intel® Core™ i7	Bluetooth version	5.2
Processor generation	12th gen Intel® Core™ i7	Ports & interfaces	
Processor model *	i7-1260P	USB 3.2 Gen 2 (3.1 Gen 2) Type-A ports quantity *	4
Processor cores	12	Intel® Thunderbolt 4	✓
Processor boost frequency	4.7 GHz	Thunderbolt 4 ports quantity	1
Processor cache	18 MB	DisplayPorts quantity	1
Configurable TDP-down	20 W	DisplayPort version	1.4
Memory		HDMI ports quantity *	2
Internal memory *	16 GB	Ethernet LAN (RJ-45) ports	1
Internal memory type	DDR4-SDRAM	Combo headphone/mic port	✓
Memory slots	2x SO-DIMM	Headphone outputs	1
Memory clock speed	3200 MHz	DC-in jack	✓
Storage		Power	
Total storage capacity *	256 GB	Power supply *	150 W
Storage media *	SSD	Design	
Optical drive type *	✗	Chassis type *	Mini PC
Total SSDs capacity	256 GB	Colour name	ECO Black
Number of SSDs installed	1	Cable lock slot	✓
SSD capacity	256 GB	Cable lock slot type	Kensington
SSD interface	PCI Express 4.0	Product colour *	Black
NVMe	✓	Software	
SSD form factor	M.2	Operating system installed *	ChromeOS
Card reader integrated	✓	Processor special features	
Compatible memory cards	MicroSD (TransFlash)	CPU configuration (max)	1
Graphics			
Discrete graphics card *	✗		

Graphics		Display	
On-board graphics card *	✓	Display included *	✗
Discrete graphics card model *	Not available	Weight & dimensions	
On-board GPU manufacturer	Intel	Width *	166.5 mm
On-board graphics card model *	Intel Iris Xe Graphics	Depth *	165.8 mm
Performance		Height *	45.9 mm
Product type *	Mini PC	Weight *	800 g
Network		Packaging data	
Ethernet LAN *	✓	Package width	334 mm
Ethernet LAN data rates	10,100,1000,2500 Mbit/s	Package depth	206 mm
Cabling technology	10/100/1000Base-T(X)	Package height	69 mm
Wi-Fi *	✓	Package weight	1.8 kg
Top Wi-Fi standard	Wi-Fi 6E (802.11ax)	Certificates	
Wi-Fi standards	Wi-Fi 6E (802.11ax)	Certification	BSMI/CB/CE/FCC/UL/Energy Star/C-Tick/WiFi/RF/VCCI
Antenna type	2x2		



4711387164105



0197105164109



197105164109

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.