



DELL Broadcom 5720 DP 1Gb Internal Ethernet 1000 Mbit/s



Brand : DELL

Product code: 540-11136

Product name : Broadcom 5720 DP 1Gb

Broadcom 5720 DP 1Gb Network Interface Card Low Profile - Kit

DELL Broadcom 5720 DP 1Gb Internal Ethernet 1000 Mbit/s:

The BROADCOM™ 5720 DP 1Gb PCI Network Interface Card in a low-profile form factor from Dell™ is responsible for connecting your desktop and server to your network. Its Remote management support enables you to maximize management resources. This product has been tested and validated on Dell systems. It is supported by Dell Technical Support when used with a Dell system.

- Features a compact design.
- Ideal for high-performance network applications.

This product is compatible with the following systems:

- PowerEdge R320
- PowerEdge R520
- PowerEdge R720

DELL Broadcom 5720 DP 1Gb. Internal. Connectivity technology: Wired, Host interface: PCI, Interface: Ethernet. Maximum data transfer rate: 1000 Mbit/s

Ports & interfaces		Network	
Connectivity technology *	Wired	Ethernet LAN data rates	10,100,1000 Mbit/s
Host interface *	PCI	Cabling technology	10/100/1000BaseT(X)
Interface *	Ethernet	Wake-on-LAN ready	✓
Ethernet LAN (RJ-45) ports	2	Design	
Network		Internal *	✓
Maximum data transfer rate *	1000 Mbit/s	Compatible products	DELL: PowerEdge R320 PowerEdge R520 PowerEdge R720
Networking standards *	IEEE 802.3, IEEE 802.3ab, IEEE 802.3u	Logistics data	
Ethernet LAN	✓	Harmonized System (HS) code	85176990



5415247055587



5397063767168

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.