



APC Easy Rack PDU, Switched, 0U, 1 Phase, 3.7kW, 230V, 16A, 20 x C13 and 4 x C19 outlets, IEC60309 2P+E inlet

Brand : APC

Product code: EPDU1116S


Product name : Easy Rack PDU, Switched, 0U, 1 Phase, 3.7kW, 230V, 16A, 20 x C13 and 4 x C19 outlets, IEC60309 2P+E inlet

Easy Rack PDU, Switched, 0U, 1 Phase, 3.7kW, 230V, 16A, 20 x C13 and 4 x C19 outlets, IEC60309 2P+E inlet

APC Easy Rack PDU, Switched, 0U, 1 Phase, 3.7kW, 230V, 16A, 20 x C13 and 4 x C19 outlets, IEC60309 2P+E inlet. PDU types: Metered, Switched, Rack capacity: 0U, Type: Single-phase. AC outlets quantity: 24 AC outlet(s), AC outlet types: C13 coupler, C19 coupler, Power plug: IEC309. Monitoring: Current, Power, Voltage, Outlet control: Lock-out, Recycle, Turn off, Turn on. Nominal input voltage: 230 V, Maximum current: 16 A



Design		Ports & interfaces	
PDU types *	Metered, Switched	Power plug	IEC309
Type	Single-phase	AC outlet types *	C13 coupler, C19 coupler
Rack capacity *	0U	Features	
Mounting	Vertical	Daisy chain	✓
Housing material	Aluminium	Management features	
Product colour	Black	Monitoring	Current, Power, Voltage
Display	LCD	Outlet control	Lock-out, Recycle, Turn off, Turn on
On/off switch	✗	Power	
Ports & interfaces		Nominal input voltage *	230 V
AC outlets quantity *	24 AC outlet(s)	Maximum current *	16 A



0731304405139



731304405139

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.