



APC Battery Replacement Cartridge APCRBC161 (OEM)

Brand : APCProduct code: APCRBC161

Product name : Battery Replacement Cartridge APCRBC161 (OEM)



Battery Replacement Cartridge APCRBC161 (OEM)

APC Battery Replacement Cartridge APCRBC161 (OEM):

The genuine APC Replacement Battery Cartridge (RBC) is tested and certified for 100% compatibility to the the specific APC UPS. This lead-acid RBC has a lifetime of three to five years which offers reliable support and extends the useful life of your UPS. The APC RBC comes fully assembled and ready for use. To see the compatible UPS list, please click View Compatible UPS Modelsbutton in Get Support Section at APC.com

APC Battery Replacement Cartridge APCRBC161 (OEM). Battery technology: Lead acid, Battery voltage: 24 V, Battery capacity: 9 Ah. Compliance certificates: RoHS, Certification: RoHS, REACH. Weight: 5.13 kg, Width: 302 mm, Height: 66 mm. Package width: 417 mm, Package height: 180 mm, Package depth: 185 mm. Quantity per pack: 1 pc(s)

Features		Weight & dimensions	
Battery technology *	Lead acid	Height	66 mm
Battery voltage *	24 V	Depth	109 mm
Battery capacity *	9 Ah	Packaging data	
Number of batteries included *	1 pc(s)	Package width	417 mm
Product colour	Black	Package height	180 mm
Certificates		Package depth	185 mm
Compliance certificates	RoHS	Package weight	5.58 kg
Certification	RoHS, REACH	Logistics data	
Weight & dimensions		Quantity per pack	1 pc(s)
Weight	5.13 kg	Harmonized System (HS) code	85079080
Width	302 mm	Total carbon footprint (kg of CO2e)	18.14



0731304338680



731304338680

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.