

ZYXEL

Zyxel ANT2105-ZZ0201F network antenna Omni-directional antenna N-type 7 dBi

Brand : Zyxel

Product code: ANT2105-ZZ0201F

Product name : ANT2105-ZZ0201F

ANT2105 Dual Pack - Dual Band Radio
Zyxel ANT2105-ZZ0201F. Antenna gain level (max): 7 dBi, Frequency band: 2.4/5 GHz, Antenna gain (2.4 GHz): 4.5 dBi. Antenna type: Omni-directional antenna, Antenna connector type: N-type, Polarization: Vertical polarization. Height: 183 mm, Diameter: 2.2 cm, Weight: 70 g



Performance		Features	
Frequency band *	2.4/5 GHz	Antenna type *	Omni-directional antenna
Antenna gain (2.4 GHz)	4.5 dBi	Antenna connector type *	N-type
Antenna gain (5 GHz)	7 dBi	Polarization	Vertical polarization
Impedance	50 Ω	Product colour	White
Horizontal beam width	360°	Purpose	Outdoor
Vertical beam width	30°	Operational conditions	
Horizontal beam width (2.4 GHz)	360°	Operating temperature (T-T)	-10 - 70 °C
Vertical beam width (2.4 GHz)	30°	Operating relative humidity (H-H)	0 - 95%
Horizontal beam width (5 GHz)	360°	Weight & dimensions	
Vertical beam width (5 GHz)	15°	Height	183 mm
Antenna gain level (max) *	7 dBi	Diameter	2.2 cm
		Weight	70 g
		Logistics data	
		Harmonized System (HS) code	85177100



4718937609413

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.