

Epson Expression Home XP-3200 Inkjet A4 5760 x 1440 DPI 33 ppm Wi-Fi

Brand : Epson

Product family: Expression

Product code: C11CK66401

Product name : XP-3200

4 Colour Multifunction Printers

Epson Expression Home XP-3200. Print technology: Inkjet, Printing: Colour printing, Maximum resolution: 5760 x 1440 DPI, Print speed (colour, normal quality, A4/US Letter): 15 ppm. Copying: Colour copying. Scanning: Colour scanning, Optical scanning resolution: 1200 x 2400 DPI. Duplex functions: Print. Maximum ISO A-series paper size: A4. Wi-Fi. Direct printing. Product colour: Black



Printing		Paper handling	
Print technology *	Inkjet	Non-ISO print media sizes	Legal, Letter
Printing *	Colour printing	Envelopes sizes	10, C6, DL
Duplex printing *	✓	Photo paper sizes (imperial)	3.5x5, 4x6, 5x7, 5x8, 8x10
Maximum resolution *	5760 x 1440 DPI	Ports & interfaces	
Print speed (black, normal quality, A4/US Letter) *	33 ppm	Direct printing *	✓
Print speed (colour, normal quality, A4/US Letter)	15 ppm	USB port	✓
Print speed (ISO/IEC 24734) black	10 ppm	USB 2.0 ports quantity	1
Print speed (ISO/IEC 24734) colour	5 ppm	Network	
Borderless printing	✓	Wi-Fi *	✓
Copying		Ethernet LAN *	✗
Copying *	Colour copying	Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)
Scanning		Mobile printing technologies	Apple AirPrint
Scanning *	Colour scanning	Design	
Optical scanning resolution *	1200 x 2400 DPI	Product colour *	Black
Scanner type *	Flatbed scanner	Market positioning *	Home & office
Scan technology	CIS	Built-in display *	✓
Input colour depth	48 bit	Display	LCD
Output colour depth	24 bit	Display diagonal	3.66 cm (1.44")
Input greyscale depth	16 bit	Power	
Fax		AC input voltage	100 - 240 V
Faxing *	✗	AC input frequency	50 - 60 Hz
Features		System requirements	
Duplex functions *	Print	Windows operating systems supported	Windows 10, Windows 8, Windows 7, Windows 8.1, Windows 11
Number of print cartridges *	4	Mac operating systems supported	Mac OS X 11.0 Big Sur, Mac OS X 12.0 Monterey, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
Printing colours *	Black, Cyan, Magenta, Yellow		
Country of origin	Indonesia		
Input & output capacity		Weight & dimensions	
Total number of input trays *	1	Width	375 mm
Total input capacity *	100 sheets	Depth	300 mm
Total output capacity *	100 sheets	Height	170 mm
Paper handling		Weight	4.3 kg
Maximum ISO A-series paper size *	A4	Packaging data	
Paper tray media types *	Envelopes, Photo paper, Plain paper	Package width	384 mm
ISO A-series sizes (A0...A9) *	A4, A5, A6	Package depth	438 mm
ISO B-series sizes (B0...B9)	B5	Package height	243 mm

Packaging data	
Package weight	5.2 kg
Packaging content	
Cables included	AC
Logistics data	
Harmonized System (HS) code	8443310000



8715946702728

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.