

StarTech.com 5in White Micro USB to USB OTG Host Adapter M/F

Brand : StarTech.com

Product code: UUSBOTGW

Product name : 5in White Micro USB to USB OTG Host Adapter M/F

StarTech.com 5in White Micro USB to USB OTG Host Adapter M/F - Micro USB Male to USB A Female On-The-Go Host Cable Adapter - White

StarTech.com 5in White Micro USB to USB OTG Host Adapter M/F. Cable length: 0.127 m. Connector 1: Micro-USB B, Connector 2: USB A, USB version: USB 2.0, Connector gender: Male/Female, Connector contacts plating: Nickel, Product colour: White



Features		Weight & dimensions	
USB version *	USB 2.0	Cable length *	0.127 m
Connector 1 *	Micro-USB B	Weight	7 g
Connector 2 *	USB A	Packaging data	
Connector gender	Male/Female	Package width	90 mm
Connector 1 gender *	Male	Package depth	125 mm
Connector 2 gender *	Female	Package height	9 mm
Connector 1 form factor	Straight	Package weight	9 g
Connector 2 form factor	Straight	Packaging content	
AWG wire size	28	Quantity per pack *	1 pc(s)
Connector contacts plating	Nickel	Certificates	
Cable jacket material	Polyvinyl chloride (PVC)	Compliance certificates	RoHS
Cable shielding	Aluminum mylar foil	Logistics data	
Product colour *	White	Harmonized System (HS) code	84733080



0065030857192



065030857192



7258006525369

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.