



Canon FA-RG1 Premium Fine Art Rough Paper, A4, 25 sheets

Brand : Canon

Product code: 4562C001


Product name : FA-RG1 Premium Fine Art Rough Paper, A4, 25 sheets

FA-RG1 Premium Fine Art Rough Paper, A4, 25 sheets

Canon FA-RG1 Premium Fine Art Rough Paper, A4, 25 sheets:

Canon Premium Fine Art Rough Paper A4 paper is high quality cotton paper developed to produce the best image quality with pigment ink. Its rough texture is ideal for expressing depth in an image and adding three-dimensional touch. Professional, experienced enthusiast photographers and art lovers will enjoy printing photos and other fine artwork on this paper. Suitable for long-term storage, this paper has a satisfying roughness, thickness and luxury touch, meaning your artwork will truly shine. Combined with genuine Canon LUCIA PRO ink in which the ink formulation has been optimised, resulting prints are rich in colour and black density and thanks to the paper’s 100 percent cotton base, image longevity and high durability are assured.

Canon FA-RG1 Premium Fine Art Rough Paper, A4, 25 sheets. Media weight: 320 g/m², Paper size: A2, Sheets per pack: 25 sheets



Features		Features	
Paper size	A2	Printing media thickness	540 µm
Media weight *	320 g/m²	Logistics data	
Sheets per pack	25 sheets	Harmonized System (HS) code	37032000



4549292170375

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.