

## Brother BWP-1D300-060 printer ribbon Black

**Brand :** Brother

**Product code:** BWP-1D300-060

**Product name :** BWP-1D300-060



- High capacity at 300 metres length per ribbon
- 60mm in width
- High quality thermal transfer ink ribbon
- Ensure clear, durable results
- Premium wax with black ink
- Requires compatible label roll

The BWP-1D300-060 premium wax thermal transfer black ink ribbon, 300 metres in length and 60mm in width has been Certified by Brother International Europe.

**Brother BWP-1D300-060 printer ribbon Black:**



This high capacity premium wax ribbon has been developed to meet your professional label printing needs. For use in retail, healthcare and logistics, you can use these 60mm wide ribbons for barcode printing and a variety of other applications. Wax thermal transfer ribbons are cost-effective and best suited to standard paper labels. The BWP-1D300-060 premium wax ribbons are used in conjunction with compatible label rolls in your thermal transfer label printer.

| Performance                           |                                                                                  | Weight & dimensions             |            |
|---------------------------------------|----------------------------------------------------------------------------------|---------------------------------|------------|
| Printing colours                      | Black                                                                            | Depth                           | 60 mm      |
| Print technology                      | Thermal transfer                                                                 | Height                          | 60 mm      |
| Product colour                        | Black                                                                            | Weight                          | 186 g      |
| Country of origin                     | Spain                                                                            | Ribbon width                    | 6 cm       |
| Brand compatibility                   | Brother                                                                          | Ribbon length                   | 300 m      |
| Compatibility *                       | TD-4520TN, TD-4420TN,<br>TD-4650TNWB, TD-4650TNWBR,<br>TD-4750TNWB, TD-4750TNWBR | <b>Packaging data</b>           |            |
|                                       |                                                                                  | Package weight                  | 2.56 kg    |
| Technical details                     |                                                                                  | Logistics data                  |            |
| Master (outer) cases per pallet layer | 13 pc(s)                                                                         | Products per pallet             | 1248 pc(s) |
| Layers per pallet                     | 8 pc(s)                                                                          | Pallet gross weight             | 285.5 kg   |
| Pallet type                           | 800 x 1200 mm                                                                    | Pallet gross height             | 11.5 cm    |
| Weight & dimensions                   |                                                                                  | Master (outer) cases per pallet | 104 pc(s)  |
| Width                                 | 60 mm                                                                            | Harmonized System (HS) code     | 84439990   |



5014047600357



5014047600425

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.