



DELL C5RHH network transceiver module Fiber optic 10000 Mbit/s SFP+ 850 nm

Brand : DELL

Product code: C5RHH

Product name : C5RHH

SFP+ SR Optic, 10GbE, 850nm

DELL C5RHH network transceiver module Fiber optic 10000 Mbit/s SFP+ 850 nm:

The Dell™ SFP+ transceiver delivers fiber connectivity to extend the range of your network. This hot-pluggable transceiver with SFP+ (Small Form Factor Pluggable) footprint features a SFP+ connector. The Dell networking 10GBase SFP+ transceiver provides 10GbE connectivity.

Additionally, it provides a unique enhanced digital diagnostic monitoring interface, which allows real-time access to device operating parameters such as transceiver temperature, laser bias current, transmitted optical power, received optical power, and transceiver supply voltage.

DELL C5RHH. SFP transceiver type: Fiber optic, Maximum data transfer rate: 10000 Mbit/s, Interface type: SFP+. Product colour: Stainless steel, Brand compatibility: Dell, Compatible products: - PowerEdge R730xd XL - PowerEdge FC630 - PowerEdge R330 - PowerEdge T430 - PowerEdge R540 - Quantity per pack: 1 pc(s)



Performance		Features	
SFP transceiver type *	Fiber optic		- PowerEdge R730xd XL - PowerEdge FC630 - PowerEdge R330 - PowerEdge T430 - PowerEdge R540 - PowerEdge T140 - PowerVault NX440 - PowerEdge R6415 - PowerEdge R840 - PowerEdge R810 - PowerEdge R715 - PowerEdge R530 - PowerEdge XR2 - PowerEdge R720XD - PowerEdge T330 - PowerEdge R7415 - PowerEdge R6525 - PowerEdge R815 - PowerVault ME4084 - PowerEdge R940xa - PowerEdge R6515 - PowerEdge R730 - PowerEdge R440 - PowerEdge C4140 - PowerEdge R240 - PowerEdge R230 - PowerEdge T440 - PowerEdge FC640 - PowerEdge T640 - PowerEdge T630 - PowerEdge R930 - PowerVault ME4024 - PowerEdge C4130 - PowerEdge R730XD - PowerEdge R940 - PowerEdge C6420 - PowerEdge R7425 - PowerEdge R740xd2 - PowerEdge R740XD - PowerEdge T340 - PowerEdge FC830 - PowerVault ME4012 - PowerEdge R820 - PowerEdge FC430 - PowerEdge R430 - PowerEdge R740 - PowerEdge R340 - PowerEdge R7515 - PowerEdge C6525 - PowerEdge R630 - PowerEdge T130 - PowerEdge M640 VRTX - PowerEdge R640 - PowerEdge M640
Maximum data transfer rate *	10000 Mbit/s		
Interface type *	SFP+		
SFP transceiver standard	SR		
Wavelength	850 nm		
Features		Compatible products	
Product colour	Stainless steel		
Brand compatibility	Dell		
		Packaging content	
		Quantity per pack	1 pc(s)



5397184186930



5715063060285

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.