

StarTech.com Industrial RS232 to RS422/485 Serial Port Converter with 15KV ESD Protection

Brand : StarTech.com

Product code: IC232485S

Product name : Industrial RS232 to RS422/485 Serial Port Converter with 15KV ESD Protection

StarTech.com Industrial RS232 to RS422/485 Serial Port Converter w/ 15KV ESD Protection - RS232 to RS422 RS485 Converter Adapter
StarTech.com Industrial RS232 to RS422/485 Serial Port Converter with 15KV ESD Protection. Width: 59 mm, Depth: 117 mm, Height: 22 mm. Input voltage: 110 - 240 V, Input current: 0.3 A. Housing material: Steel. Certification: CE, FCC, REACH



Technical details		Weight & dimensions	
Host interface *	RS-232	Depth	117 mm
Output interface *	RS-232	Height	22 mm
Connector 1	DB-9	Weight	143 g
Connector 2	DB-9	Package width	208 mm
Connector gender	Male/Female	Package depth	146 mm
Product colour	Black	Package height	41 mm
Maximum cable length	1200 m	Package weight	351 g
Compliance certificates	RoHS	Power	
Operational conditions		Input voltage	110 - 240 V
Operating temperature (T-T)	0 - 50 °C	Input current	0.3 A
Storage temperature (T-T)	-20 - 60 °C	Material	
Operating relative humidity (H-H)	5 - 85%	Housing material	Steel
Weight & dimensions		Certificates	
Width	59 mm	Certification	CE, FCC, REACH
		Packaging data	
		Manual	✓



0065030852555



065030852555



5054629356784

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.