

Targus HyperDrive 4K 2 x USB 3.2 Gen 2 (3.1 Gen 2) Type-C Silver

Brand : Targus
Product code: HD156-GL
Product name : HyperDrive 4K



- Connect Up To 3 Displays at 4K 60Hz
 - Use HDMI Or DisplayPort
 - Easy Driverless Setup
 - Enjoy 15 Essential Ports
 - Ergonomic, Heat Dissipating Design
 - Also Works With 13-14" MacBooks
- HDMI, Ethernet, MicroSD, SD, 3xDisplayPort, 3xUSB-A, 3xUSB-C, 34.95x5.2x1.65 cm, 0.3 kg, Silver
- Targus HyperDrive 4K. Host interface: 2 x USB 3.2 Gen 2 (3.1 Gen 2) Type-C, USB Power Delivery up to: 100 W. Product colour: Silver, Compatible memory cards: MicroSD (TransFlash), SD, Maximum refresh rate: 60 Hz. Width: 52 mm, Depth: 35 mm, Height: 16.5 mm

Ports & interfaces		Network	
Host interface *	2 x USB 3.2 Gen 2 (3.1 Gen 2) Type-C	Ethernet LAN (RJ-45) ports	1
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity *	2	Performance	
USB 3.2 Gen 1 (3.1 Gen 1) Type-C ports quantity	2	Card reader integrated *	✓
USB 3.2 Gen 2 (3.1 Gen 2) Type-A ports quantity	1	Compatible memory cards	MicroSD (TransFlash), SD
USB Power Delivery up to	100 W	Maximum refresh rate	60 Hz
HDMI ports quantity *	3	Product colour *	Silver
DisplayPorts quantity	3	Hub interfaces	DisplayPort, HDMI, RJ-45, USB 3.2 Gen 1 (3.1 Gen 1) Type-A, USB 3.2 Gen 1 (3.1 Gen 1) Type-C
Weight & dimensions			
		Width	52 mm
		Depth	35 mm
		Height	16.5 mm
		Weight	300 g



6941921147976

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.