

StarTech.com 1m Serial Attached SCSI SAS Cable - SFF-8087 to 4x Latching SATA

Brand : StarTech.com

Product code: SAS8087S4100

Product name : 1m Serial Attached SCSI SAS Cable - SFF-8087 to 4x Latching SATA



1m Serial Attached SCSI SAS Cable - SFF-8087 to 4x Latching SATA

StarTech.com 1m Serial Attached SCSI SAS Cable - SFF-8087 to 4x Latching SATA:

Connect a SATA/SAS Controller to 4 SATA drives
The SAS8087S4100 SFF-8087 to 4x SATA SAS cable features one 36-pin plug (SFF-8087), which fans out to four SATA 7-pin receptacles, providing a reliable solution for connecting a SATA HDD to a SAS controller or backplane.
Designed and constructed for long-lasting dependability and reliability, the 1m (39.37in) SFF-8087 to 4x SATA SAS cable is backed by lifetime warranty.
The StarTech.com Advantage
- Provides reliable, high-performance SAS/SATA drive and backplane connectivity
- Latching SATA and SAS connectors eliminate accidental disconnections
- Backed by StarTech.com lifetime warranty
StarTech.com 1m Serial Attached SCSI SAS Cable - SFF-8087 to 4x Latching SATA. Cable type: SATA III, Cable length: 1 m, Connector 1: SATA 7-pin. Weight: 100 g. Package width: 125 mm, Package depth: 225 mm, Package height: 22 mm



Features		Weight & dimensions	
Product colour *	Red, Black	Weight	100 g
Cable type *	SATA III	Packaging data	
Cable length *	1 m	Package width	125 mm
Connector 1 *	SATA 7-pin	Package depth	225 mm
Connector gender	Male/Female	Package height	22 mm
		Package weight	85 g



0065030846998



065030846998



0163120858385



163120858385

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.