



APC Performance, Vertical Cable Manager for 2 & 4 Post Racks,
84"H x 12"W, Double-Sided with Doors

Brand : APC

Product code: AR8675

Product name : Performance, Vertical Cable Manager for 2
& 4 Post Racks, 84"H x 12"W, Double-Sided with Doors

Performance, Vertical Cable Manager for 2 & 4 Post Racks, 84"H x 12"W, Double-Sided with Doors

APC Performance, Vertical Cable Manager for 2 & 4 Post Racks, 84"H x 12"W, Double-Sided with Doors:

This 12" wide, high capacity vertical cable manager AR8675 for 2 and 4 Post open frame racks features a double-sided cable channel with multiple internal cable tie-off locations and smooth plastic fingers at 1U increments for organized patching applications.

APC Performance, Vertical Cable Manager for 2 & 4 Post Racks, 84"H x 12"W, Double-Sided with Doors.
Type: Cable management panel, Product colour: Black. Weight: 36.3 kg

Features		Weight & dimensions	
Type *	Cable management panel	Weight	36.3 kg
Product colour *	Black	Packaging data	
Built-in fan	✗	Package width	826 mm
Hot-swap	✗	Package depth	2287 mm
On/off switch	✗	Package height	456 mm
Castor wheels	✗	Package weight	45.4 kg
Locking	✗	Technical details	
Certification	REACH, UL	Total carbon footprint (kg of CO2e)	137.76
Weight & dimensions		Compliance certificates	RoHS
Width	304 mm	Logistics data	
Depth (max)	66 cm	Harmonized System (HS) code	85389099
Height	2134 mm		



7313042916196



0731304291619



731304291619

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.