



TP-Link 8-Port 10/100Mbps + 3-Port Gigabit Desktop Switch with 8-Port PoE+

Brand : TP-Link

Product code: TL-SL1311MP

Product name : 8-Port 10/100Mbps + 3-Port Gigabit Desktop Switch with 8-Port PoE+



- 8× 10/100 Mbps RJ45 Ports, 2× Gigabit RJ45 Ports, 1× Gigabit SFP Port
 - 8× PoE+ ports transfer data and power on individual cables
 - Works with IEEE 802.3af/at compliant PDs
 - Supports PoE Power up to 30 W for each PoE port
 - Supports PoE Power up to 124 W for 8 PoE ports*
 - Up to 250 m data and power transmitting range under Extend Mode**
 - Isolation Mode allows one-click client traffic separation for higher security and performance
 - PoE Auto Recovery guarantees stable operation of PoE devices by automatically rebooting the dropped or unresponsive PD devices
 - Fanless Design reduces power consumption and works silently in its location
 - Plug and play with no configuration required
- 8× 10/100 Mbps 802.3af/at PoE+ Ports, 2× Gigabit RJ45 Ports, 1× Gigabit SFP Port, 209 × 126 × 26 mm


Management features		Power	
Switch type *	Unmanaged	Power supply included *	✓
Ports & interfaces		Number of power supply units	1
Basic switching RJ-45 Ethernet ports quantity *	10	DC input voltage	53.5 V
Basic switching RJ-45 Ethernet ports type *	Fast Ethernet (10/100)	Input current	2.43 A
SFP module slots quantity	1	Power over Ethernet (PoE)	
Power connector	DC-in jack	Power over Ethernet (PoE) *	✓
Network		Power over Ethernet plus (PoE+) ports quantity	8
Networking standards *	IEEE 802.3af, IEEE 802.3at	Total Power over Ethernet (PoE) budget	124 W
10G support *	✗	Operational conditions	
Copper ethernet cabling technology	10BASE-T, 100BASE-TX	Operating temperature (T-T)	0 - 40 °C
Cable types supported	Cat3, Cat4, Cat5, Cat5e	Storage temperature (T-T)	-40 - 70 °C
Auto MDI/MDI-X	✓	Operating relative humidity (H-H)	10 - 90%
Auto-negotiation	✓	Storage relative humidity (H-H)	5 - 90%
Data transmission		Weight & dimensions	
Switching capacity *	7.6 Gbit/s	Width	209 mm
Forwarding rate	5.6544 Mpps	Depth	126 mm
MAC address table *	2000 entries	Height	26 mm
Store-and-forward	✓	Packaging content	
Jumbo frames support	✓	Manual	✓
Jumbo frames	16000	Packaging data	
Design		Package type	Box
Rack mounting *	✗	Logistics data	
Product colour	Black	Harmonized System (HS) code	85176990
Number of fans	0 fan(s)		



6935364006266




6935364006259



0840030702358



840030702358



1210002617215



1210002617208

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.