



QNAP QXG-2G1T-I225 network card Internal Ethernet 2500 Mbit/s

Brand : QNAP

Product code: QXG-2G1T-I225

Product name : QXG-2G1T-I225

2.5G LAN, RJ-45, PCIe x1 2.0,

QNAP QXG-2G1T-I225 network card Internal Ethernet 2500 Mbit/s:

2.5 GbE network expansion card

2.5 GbE network expansion card delivers speeds of up to 2.5 Gbps. You can easily upgrade your home and office network infrastructure with existing cables.

QNAP QXG-2G1T-I225. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Maximum data transfer rate: 2500 Mbit/s



Ports & interfaces		Design	
Connectivity technology *	Wired	Component for *	NAS/storage server
Host interface *	PCI Express	Internal *	✓
Interface *	Ethernet	System requirements	
Ethernet LAN (RJ-45) ports	1	Windows operating systems supported	Windows 10
PCI version	2.0	Linux operating systems supported	✓
Network		Server operating systems supported	Windows Server 2019
Maximum data transfer rate *	2500 Mbit/s	Packaging content	
Networking standards *	IEEE 802.1Qav, IEEE 802.1Qbv, IEEE 802.1as	Mounting brackets included	✓
Ethernet LAN	✓	Quick installation guide	✓
Ethernet interface type	2.5 Gigabit Ethernet, Fast Ethernet, Gigabit Ethernet	Logistics data	
Wake-on-LAN ready	✓	Harmonized System (HS) code	85176990
LAN controller	Intel I225-LM		



0885022020010



885022020010



4713213517994

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.