

StarTech.com USB Dual VGA over Cat5 KVM Console Extender - 650 ft / 200m

Brand : StarTech.com

Product code: SV565DUTPU

Product name : USB Dual VGA over Cat5 KVM Console Extender - 650 ft / 200m



StarTech.com 650 ft/200m USB 2.0 Dual VGA KVM Console Extender over Cat5 UTP -for Dual VGA, USB-enabled PC or KVM Switch - Upto 1920x1200 (SV565DUTPU)
StarTech.com USB Dual VGA over Cat5 KVM Console Extender - 650 ft / 200m. Width: 80 mm, Depth: 155 mm, Height: 40 mm. Cables included: AC, KVM




Technical details		Weight & dimensions	
Maximum transfer distance	200 m	Package width	239 mm
Product colour	Black	Package depth	367 mm
Compliance certificates	RoHS	Package height	75 mm
Ports & interfaces		Package weight	2.25 kg
VGA (D-Sub) ports quantity	4	Operational conditions	
USB 2.0 ports quantity	12	Operating temperature (T-T)	0 - 40 °C
RJ-45 ports quantity	2	Storage temperature (T-T)	-10 - 60 °C
DC-in jack	✓	Operating relative humidity (H-H)	0 - 80%
Weight & dimensions		Packaging content	
Width	80 mm	Cables included	AC, KVM
Depth	155 mm	Manual	✓
Height	40 mm	Logistics data	
Weight	535 g	Harmonized System (HS) code	84733020



0065030848237



065030848237



0100177416465



100177416465

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.