Epson Golf ball Singlepack Black 34 DURABrite Ultra Ink





Brand : Epson **Product family:** Golf ball **Product code:** C13T34614010

Product name : Singlepack
Black 34 DURABrite Ultra Ink

Singlepack Black 34 DURABrite Ultra Ink
Epson Golf ball Singlepack Black 34 DURABrite Ultra Ink. Cartridge capacity: Standard Yield, Black ink type: Pigment-based ink, Black ink volume: 6.1 ml, Printing colours: Black, Quantity per pack: 1 pc(s), Black ink page yield: 350 pages

Features	
Black ink type	Pigment-based ink
Print technology	Inkjet printing
Compatibility *	- WorkForce Pro WF-3725DWF - WorkForce Pro WF-3720DWF
Quantity per pack *	1 pc(s)
Black ink cartridges quantity	1
Black ink volume	6.1 ml
Black ink page yield *	350 pages
Type *	Original
Cartridge capacity	Standard Yield
Ink type	Pigment-based ink
Printing colours *	Black
Brand compatibility *	Epson
OEM code	C13T34614010
Country of origin	Indonesia

Packaging data	
Package width	102 mm
Package depth	26 mm
Package height	145 mm

Packaging data	
Package weight	40 g
Package type	Blister

Logistics data	
Products per pallet	3400 pc(s)
Pallet gross weight	0 g
Master (outer) case width	102 mm
Master (outer) case length	260 mm
Master (outer) case height	146 mm
Products per master (outer) case	10 pc(s)
Master (outer) case gross weight	0 g
Master (outer) case GTIN (EAN/UPC)	8715946632476
Harmonized System (HS) code	84439990
Pallet weight (UK)	0 g
Products per pallet (UK)	3400 pc(s)
Products per pallet layer	340 pc(s)
Products per pallet layer (UK)	340 pc(s)
Minimum order quantity	10 pc(s)

8715946632032

4058154209042

5057454714088

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date