

October 2012

**PRODUCT DATA SHEET**

<b>Product</b>	<b>High Heat Black Matt Paint</b>
<b>Type</b>	Solvent based Silicone Alkyd High Heat Paint.
<b>Intended Use</b>	The paint is only suitable for use on ferrous metals such as wood burning stoves, barbeques, domestic and industrial stoves, furnace chimneys, grates and exhausts.
<b>Special Features</b>	A fast drying, protective and decorative paint suitable for temperatures of up to 600° C
<b>Preparation</b>	The surface must be clean, dry and free from grease, dust rust and other contaminants. Remove all rust with a scraper or use Rustins Rust Remover. If the product should only be applied to bare metal and not previously coated surfaces.
<b>Application</b>	Stir well before use until there is no sediment on the bottom of the tin. Apply with a bristle paint brush. The paint may be sprayed but may require dilution with Xylene Thinners.
<b>Coats</b>	Only one light coat should be applied. If a heavy coat or more than one coat is applied it is possible that the paint will flake from the surface.
<b>Drying Time</b>	The surface will be touch dry within 15 minutes and can be handled in 1 hour in good conditions. The painted article if air dried will become fully cured once it has been heated up to between 200 - 220° C for approximately 20 minutes.
<b>Re-coating Time</b>	The paint should not be recoated.
<b>Application Temp.</b>	Ideally 15-25°C. Do not use below 10°C, or in conditions of high humidity.
<b>Coverage</b>	15 sq metres per litre per coat depending type of application and surface.
<b>Maintenance</b>	The previous coat will need to be removed if recoating becomes necessary.
<b>Compatibility</b>	N/A
<b>Settlement</b>	Stir well before use.
<b>Shelf-life/Storage</b>	The shelf life of the product is 2 years. It is preferable to store the product in a cool place. It is important to replace the lid and ensure an airtight seal after use. <b>NOTE:</b> The product may be used after shelf life has expired but should first be checked to ensure that there is no deterioration of quality.
<b>Hazards</b>	Flammable. Keep out of reach of children. Keep away from sources of ignition- no smoking. Avoid contact with skin and eyes. Use only in well ventilated areas. A full Safety Data Sheet is available upon request or on <a href="http://www.rustins.co.uk">www.rustins.co.uk</a>
<b>Clean-Up</b>	Remove as much product as possible from brushes before cleaning. Clean whilst wet with <b>Rustin Cellulose Thinners</b> or Xylene based Thinners. Hard brushes can be cleaned with <b>Rustins Brush Restorer</b> .
<b>Sizes</b>	250ml 500ml