

EXTERNAL DESKTOP POWER SUPPLY

9VDC 18WATT

T5794ST



Features:

- Universal Input
- IEC-320-C8 Input Connector
- 3 Year Warranty
- Efficiency Level VI
- Safety approved to: UL,CUL,FCC,GS,CE,RCM



Description:

The Stontronics Range of 18 watt AC/DC switch mode power supplies provide 18 watts of continuous output power in a high quality compact enclosure suitable for many general power applications.

Specification	
RS Stock No.	T5794ST
Input Voltage Range	90 → 264 V ac
Input Frequency Range	50 → 60Hz
Input Connector	IEC 320-C8
Input Current Rated	500mA Rms Max
Inrush Current	50A Max. at 115VAC cold start
	100A Max. at 230VAC cold start
Leakage Current	<0.25mA
Efficiency	85.45% Min
Input Power(Output: No Load)	<0.1W (CEC & DOE LEVEL VI Compliant)
Output Voltage Rating	9 V dc
Output Current Range	2A
Output Min Current	0A
Output Connection Type	2.1 x 5.5 x 12 mm Centre Positive - Right Angle
Line and Load Regulation	+/-5%
Over Voltage Protection	<2.0A
Over Load Protection	⊠ 3A output load
Short Circuit Protection	Output shut down auto recover
Ripple Voltage	150 mV (p-p) (100V-240V AC Input)
Hi-Pot	3000Vac or 4242VDC 10mA 1 min
Safety Approved	UL,CUL,FCC,GS,CE,RCM,LVD
EMI Standard	Meet FCC Class B, CE
Operating Temperature Range	0 → 40 °C
Storage Temperature	-10 to 70°C
Operating Humidity	20% to 80%
Storage Humidity	10% to 90%
Dimensions	(L) 80.6 x (W) 50 x (H) 31mm
Product Weight	130 gm
Regulator Type	Switched Mode Power Supply

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.







TT Electronics | Stontronics Ltd
Chancerygate Business Centre, Cradock Road, Reading RG2 0AH, UK
t: +44 (0) 118 931 1199

EXTERNAL DESKTOP POWER SUPPLY 9VDC 18WATT

T57945T



Diagrams



General Note
TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | Stontronics Ltd
Chancerygate Business Centre, Cradock Road, Reading RG2 0AH, UK
t: +44 (0) 118 931 1199