

# 454 Imperial T-handle hexagon screwdriver Hex-Plus, imperial, 7/64" x 150 mm

Series 400 T-Handle



<b>EAN:</b>	4013288208088	<b>Size:</b>	182x78x15 mm
<b>Part number:</b>	05023358001	<b>Weight:</b>	26 g
<b>Article number:</b>	454 Imperial	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- T-handle screwdriver for the transmission of particularly high tightening and loosening moments
- Ergonomic 2-component handle with finger handle recesses and pleasant surface feel for very high power transmission and fatigue-free working.
- Take it easy tool finder: colour coding according to profile and size
- With additional short arm for the transmission of extremely high torques due to the leverage of the long arm

T-handle screwdriver: The ideal handle shape to allow high torque transmission in difficult tightening and loosening situations. The ergonomic shape of the handle fills the palm of the hand well, the fingers lie safely in the soft rounded handle recesses. The whole hand makes contact with the handle and friction losses between the hand and the handle are avoided. Special surface treatment of the blades for high corrosion protection and an optimum fit in the screw head.

## Web link

[https://products.wera.de/en/screwdrivers\\_series\\_400\\_t-handle\\_454\\_imperial.html](https://products.wera.de/en/screwdrivers_series_400_t-handle_454_imperial.html)

Wera - 454 Imperial  
05023358001 - 4013288208088

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Series 400 T-Handle

**Ergonomic 2-component T-handle**



The ergonomically shaped 2-component T-handle with finger recesses and pleasant surface facilitates very high power transmission and fatigue-free working.

**Second arm**



The additional short arm, which emerges laterally from the handle, allows the transmission of extremely high torques by using the long arm as a lever.


**Corrosion protection and fitting accuracy**



Due to the special surface treatment, the blades receive a high level of corrosion protection. The optimum fitting accuracy of the screw is also guaranteed.

**Hex-Plus**

**"Take it easy" Tool Finder**



Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

**Web link**

[https://products.wera.de/en/screwdrivers\\_series\\_400\\_t-handle\\_454\\_imperial.html](https://products.wera.de/en/screwdrivers_series_400_t-handle_454_imperial.html)

Wera - 454 Imperial  
05023358001 - 4013288208088

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

Further versions in this product family:



inch



mm



mm



mm



mm



inch

05023356001	5/64	150	12	32	65	6
05023357001	3/32	150	12	32	65	6
<b>05023358001</b>	<b>7/64</b>	<b>150</b>	<b>12</b>	<b>32</b>	<b>65</b>	<b>6</b>

Web link

[https://products.wera.de/en/screwdrivers\\_series\\_400\\_t-handle\\_454\\_imperial.html](https://products.wera.de/en/screwdrivers_series_400_t-handle_454_imperial.html)

Wera - 454 Imperial

05023358001 - 4013288208088

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)