




EAN:	4013288212245	Size:	81x34x34 mm
Part number:	05008856001	Weight:	35 g
Article number:	367 TORX® Stubby	Country of origin:	CZ
		Customs tariff number:	82054000

- Short compact shape for working in confined spaces
- Ergonomic 2-component Kraftform handle for precise work
- Blades with the benefits of the Wera Bit technology
- Hexagonal anti-roll feature against rolling away
- Take it easy tool finder: colour coding according to profile and size

Especially small screwdrivers with short blades for hard to reach areas. The 2-component Kraftform handle with its practical combination of hard and soft zones allows for a firm grip and precise working. The blades have all the benefits of the Wera Bit technology. Special surface treatment of the blades for high corrosion protection and optimum fitting accuracy in the screw. The hexagon anti-roll protection prevents annoying rolling away of bits in the workplace.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_367_torx_stubby.html

Wera - 367 TORX® Stubby
05008856001 - 4013288212245

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Compact shape




With its compact handle shape and the short blade, the Kraftform Stubbies are particularly suitable for working in confined screwdriving situations.

Tangible ergonomics




The 2-component Kraftform handle allows high power transmission due to the non-slip, softer grip areas and high working speeds due to the hard grip areas, which allow a quick hand switch.

Long life




The special surface treatment of the blades sees to a high level of corrosion protection and optimum fitting accuracy of the screw.

“Take it easy” Tool Finder



Screwdrivers with “Take it easy” tool finder: colour coding according to profile and size stamp.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

Further versions in this product family:

		 mm	 mm	 mm	 inch
05008856001	TX 10	25	54	3.4	1
05008857001	TX 15	25	54	3.7	1
05008858001	TX 20	25	54	4.0	1
05008859001	TX 25	25	54	4.5	1
05008860001	TX 27	25	54	5.1	1
05008861001	TX 30	25	54	5.6	1
05008862001	TX 40	25	54	-	1

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_367_torx_stubby.html

Wera - 367 TORX® Stubby
05008856001 - 4013288212245

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

367 TORX® Stubby screwdriver, TX 10 x 25 mm

Innovations and Spring / Summer Campaign 2020



Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_367_torx_stubby.html

Wera - 367 TORX® Stubby
05008856001 - 4013288212245

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de