

PRODUCT DATA



Date: 12 July 2010 Information Sheet No.: TDS00125

EVO-STIK DECORATORS FILLER A WATER BASED ACRYLIC SEALANT

Evo-Stik Decorators Filler is a fast drying paste which sets by evaporation of water when exposed to the atmosphere. It is ideal for sealing low movement gaps around window, doorframes, skirting boards and general sealing of internal fixtures. Evo-Stik Decorators Filler will accept most paints when set. Before using this product refer to the relevant Health & Safety Data Sheet.

Uses

- Sealing gaps around window and door frames.
- · Sealing gaps in skirting boards and coving.
- Sealing gaps in plasterboard, and fine cracks prior to decorating.
- · General sealing of internal fixtures.
- Evo-Stik Decorators Filler may be used externally provided it is allowed to set in warm dry conditions, with no chance of rain during the first day.

Product Characteristics

Colour White

Form Ready to use paste; suitable for

gun or knife application.

Specific Gravity 1.48, approximately

Composition A blend of acrylic polymers and

selected fillers.

Product Code 112926 C20 x 12

Shelf life/storage 24 months from date of

manufacture when stored in original unopened containers. Store in dry conditions between

5°C and 30°C.

Typical Performance Data (approx.)

Flash Point Not applicable (water based)

Application Temperature

Range +10°C to +40°C.

Service Temperature

Range -20°C to +70°C.

Life Expectancy When applied correctly the sealant

will perform satisfactorily for approximately 15 years.

Coverage 10mm (diagonal) fillet 6mm bead

C20 12.5 metres 11.0 metres

Directions for use

IMPORTANT

Before using this Evo-Stik Decorators Filler refer to the relevant Health & Safety Data Sheet. Available at www.bostik.co.uk named as the code above.

Preparation

- Ensure that surfaces to which the product is to be applied are clean, dry and free of any contamination or loose matter.
- Very porous surfaces must be primed using a diluted PVA (5 volumes of water to 1 volume of PVA), such as Evo-Bond Building Adhesive. The primer must be allowed to dry.

Application

- Cut the dome of the tube with a sharp knife, taking care not to damage the thread, pierce the foil membrane and screw the nozzle on. Apply a continuous bead ensuring contact is made with both sides of the gap. At the end of the run, release the trigger and press the plunger release plate of the gun.
- 2. Simply removing excess filler, immediately, with a flat blade will give a nice smooth finish.



PRODUCT DATA



Date: 12 July 2010 Information Sheet No.: TDS00125

- 3. When the product is used to seal gaps the temporary use of masking tape to define the edges of the joint will often give a cleaner, neater looking seal. Always remove masking tape before the filler skins, which is 15 minutes to an hour, but is dependent upon drying conditions.
- 4. Painting of the filler should be only carried out when it has fully dried. Painting too early may lead to the paint cracking.
- 5. For fine filling and for applications less than 1mm painting may be carried out in as little as 30 minutes.
- 6. When used for sealing gaps around frames and skirtings etc. where the sealant may have a depth greater than 5mm drying times will be much longer. Leave at least 24 hours before painting.

Cleaning

- Excess product should be carefully scraped away using a knife and the remaining film wiped away immediately with a clean cloth damped with water. Warm soapy water is best, followed by rinsing and drying.
- 2. Set product can only be removed mechanically using a sharp knife or scraper.
- 3. Do not use solvent to clean product from the skin use soap and water.

Precautions in Use

Evo-Stik Decorators Filler will not be water resistant until it has dried. Painting after the product has dried will prolong the life of the product.

For health and safety instruction, first aid measures and spillage and disposal instructions, see separate Health and Safety Data Sheet for Evo-Stik Decorators Filler.



PRODUCT DATA



Date: 12 July 2010 Information Sheet No.: TDS00125

Sales & Technical contacts at Bostik	Telephone	Facsimile	Email addresses
Sales	0844 371 1192	01785 241818	customer.service@bostik.com
Technical advice	0844 371 1197	01785 272867	technical.service@bostik.com
Technical Data & COSHH (MSDS) sheets	01785 272625	01785 212962	stafford.gatehouse@bostik.com

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.