

EVO-STIK Strong Stuff Waterproof Adhesive

A SINGLE-PART, SMP POLYMER ADHESIVE

Date: 3 March 2017 Fact Sheet No.: TDS00460

YOUR SMART ADVANTAGES - High strength, waterproof grab adhesive - Sticks to wet surfaces, even underwater - Instant waterproof seal

USES

EVO-STIK Strong Stuff Waterproof Adhesive is a high performance, single component, moisture curing, Silyl Modified Polymer (SMP) adhesive. It will bond most surfaces even if both are impervious. The product will bond damp surfaces and may even be used underwater. It has very low odour, cures to form a hard elastic rubber, with almost no shrinkage and is low hazard; it does not contain any water or solvent, making it ideal for bonding foam polystyrene sheets. When fully cured the product may be painted with most types of water based emulsion paints.

EVO-STIK Strong Stuff Waterproof bonds to most surfaces including wood, concrete, brick, plaster, glass, ceramics, metals, rigid pvc, grp and foam polystyrene. It also bonds panels, signs, wallboards, insulation boards and skirting's. to the above surfaces.

PRODUCT CHARACTERISTICS	
Colour	Off white
Specific Gravity	1.62 approx.
Composition	Moisture curing SMP Polymer system
Product Code	30813032 290ml cartridges x12
Storage/Shelf Life	Store for up to 18 months when stored in the original, unopened packaging under dry conditions within

	the temperature range of +5°C to +25°C.
TYPICAL PERFORMANCE DATA (Approx.)	
Coverage	44 metres of 3mm diameter bead
	14 metres of 5mm diameter bead
Drying Times	Skin Formation: 5 to 15 minutes at 25°C
	Full Cure: 17 to 24 hours at 20°C
Shore A Hardness	50 - 55
Tensile Strength	1.5 - 1.8 MPA
Elongation At Break	200 - 300%
Movement	Will accommodate up to 12% of the mean joint width
Shrinkage	Less than 3%
Water Resistance	Excellent
Oil & Petrol Resistance	Good
Chemicals Resistance	Good
Abrasion Resistance	Good
Paintability	Cured product may be overpainted with most types of water based emulsion paints. In some rare cases the surface may retain slight tack which, often, another coat of the paint will remedy.

DIRECTIONS FOR USE

IMPORTANT: Before using EVO-STIK Strong Stuff



Waterproof refer to the relevant Health & Safety Data Sheet, available at www.bostik.co.uk.

PREPARATION

- Any loose or weak layers and any contamination on the surface must be removed.
- 2. Surfaces must be clean and preferably dry.

APPLICATION

- 3. Apply parallel beads of adhesive to one of the surfaces. Ensure that the adhesive is forced onto the surface to displace dampness.
- 4. Bring the two surfaces together, quickly after application. Then press and twist to force the adhesive onto the other surface.
- 5mm diameter beads are generally sufficient. For close fitting surfaces these may be reduced to 3mm.
- The degree of separation of the beads of EVO-STIK Serious Stuff Wet Grab Adhesive will depend upon the rigidity and weight of the panel, board or sign being bonded. If beads are separated by more than 200mm a perimeter bead should be applied.
- For rigid sheets 100 150mm separation between beads is generally sufficient for high loading, but may be increased if the load is low (such a wallboards and foam polystyrene) where 200 - 500mm is acceptable.
- 8. For less rigid boards the separation may need to be quite small and it is important to choose the correct bead size.

CLEANING

- 9. Uncured product may be removed using cloths lightly moistened with white spirit, after carefully scraping off
- 10. Cured product requires mechanical removal.

PRECAUTIONS IN USE

EVO-STIK Strong Stuff Waterproof Adhesive will not bond polythene, polypropylene & Teflon. It should not be used on bitumen contaminated surfaces. Not suitable for continuous submersion in water.

For any application not covered please contact Technical Services on +44 (0)1785 272625 or visit www.bostik.co.uk for advice.

Recommendations and suggestions are for guidance only, since conditions of use are completely beyond our control.

For health and safety instruction, first aid measures and spillage and disposal instructions, see separate Health and Safety Data Sheet for EVO-STIK Strong Stuff Waterproof, available at www.bostik.co.uk.





This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

SalesTel: 0844 371 1192Fax: 01785 241818customer.service@bostik.comTechnical AdviceTel: 0844 371 1197Fax: 01785 272867technical.service@bostik.comTechnical Data & COSHH (MSDS) Data SheetsTel: 01785 272625Fax: 01785 212962stafford.gatehouse@bostik.com

