


454 T-handle hexagon screwdriver Hex-Plus, 2.5 x 100 mm

Series 400 T-Handle



EAN:	4013288207814	Size:	132x75x15 mm
Part number:	05023332001	Weight:	24 g
Article number:	454	Country of origin:	CZ
		Customs tariff number:	82054000

- T-handle screwdriver for the transmission of particularly high tightening and loosening moments
- Ergonomic 2-component handle with finger handle recesses and pleasant surface feel for very high power transmission and fatigue-free working.
- Take it easy tool finder: colour coding according to profile and size
- With additional short arm for the transmission of extremely high torques due to the leverage of the long arm


T-handle screwdriver: The ideal handle shape to allow high torque transmission in difficult tightening and loosening situations. The ergonomic shape of the handle fills the palm of the hand well, the fingers lie safely in the soft rounded handle recesses. The whole hand makes contact with the handle and friction losses between the hand and the handle are avoided. Special surface treatment of the blades for high corrosion protection and an optimum fit in the screw head.

Web link
https://products.wera.de/en/screwdrivers_series_400_t-handle_454.html

Wera - 454
05023332001 - 4013288207814

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Ergonomic 2-component T-handle



The ergonomically shaped 2-component T-handle with finger recesses and pleasant surface facilitates very high power transmission and fatigue-free working.

Second arm




The additional short arm, which emerges laterally from the handle, allows the transmission of extremely high torques by using the long arm as a lever.

High torque transfer



By using the blade as an extension of your lower arm you can transfer particularly high torque.

Corrosion protection and fitting accuracy




Due to the special surface treatment, the blades receive a high level of corrosion protection. The optimum fitting accuracy of the screw is also guaranteed.

Hex-Plus



Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

“Take it easy” Tool Finder



Screwdrivers with “Take it easy” tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/screwdrivers_series_400_t-handle_454.html

Wera - 454

05023332001 - 4013288207814







Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

454 T-handle hexagon screwdriver Hex-Plus, 2.5 x 100 mm

Series 400 T-Handle



Further versions in this product family:

	 mm	 mm	 mm	 mm	 mm	 inch
05023330001	2	100	12	32	65	4
05023332001	2.5	100	12	32	65	4

Web link
https://products.wera.de/en/screwdrivers_series_400_t-handle_454.html

Wera - 454
05023332001 - 4013288207814