

## 495 T-handle socket wrench screwdrivers, 13 x 230 mm

### Series 400 T-Handle



<b>EAN:</b>	4013288208491	<b>Size:</b>	280x98x22 mm
<b>Part number:</b>	05023393001	<b>Weight:</b>	178 g
<b>Article number:</b>	495	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- T-handle screwdriver for the transmission of particularly high tightening and loosening moments
- Ergonomic 2-component handle with finger handle recesses and pleasant surface feel for very high power transmission and fatigue-free working.
- With handle markings by profile and size.
- Special surface treatment for high corrosion protection and optimum fitting accuracy

T-handle screwdriver: The ideal handle shape to allow high torque transmission in difficult tightening and loosening situations. The ergonomic shape of the handle fills the palm of the hand well, the fingers lie safely in the soft rounded handle recesses. The whole hand makes contact with the handle and friction losses between the hand and the handle are avoided. Special surface treatment of the blades for high corrosion protection and an optimum fit in the screw head.

#### Web link

[https://products.wera.de/en/screwdrivers\\_series\\_400\\_t-handle\\_495.html](https://products.wera.de/en/screwdrivers_series_400_t-handle_495.html)

Wera - 495  
05023393001 - 4013288208491


Wera Werkzeuge GmbH  
Korzeter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**Ergonomic 2-component T-handle**




The ergonomically shaped 2-component T-handle with finger recesses and pleasant surface facilitates very high power transmission and fatigue-free working.

**High torque transfer**




By using the blade as an extension of your lower arm you can transfer particularly high torque.

**Corrosion protection and fitting accuracy**








Due to the special surface treatment, the blades receive a high level of corrosion protection. The optimum fitting accuracy of the screw is also guaranteed.

**“Take it easy” Tool Finder**



Screwdrivers with “Take it easy” tool finder: colour coding according to profile and size stamp.

**Further versions in this product family:**

					
	mm	mm	mm	mm	inch
05023381001	5	230	38	77	9
05023382001	5.5	230	38	77	9
05023383001	6	230	38	77	9
05023384001	7	230	49	99	9
05023385001	8	230	49	99	9
05023386001	9	230	49	99	9
05023387001	10	230	49	99	9
05023389001	11	230	49	99	9
05023391001	12	230	49	99	9
<b>05023393001</b>	<b>13</b>	<b>230</b>	<b>49</b>	<b>99</b>	<b>9</b>

**Web link**

[https://products.wera.de/en/screwdrivers\\_series\\_400\\_t-handle\\_495.html](https://products.wera.de/en/screwdrivers_series_400_t-handle_495.html)

Wera - 495

05023393001 - 4013288208491

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)