



EAN: 4013288220608

Part number: 05004175001

Article number: Bicycle Set 7

Size: 330x150x70 mm

Weight: 1852 g

Country of origin: CZ

Customs tariff number: 82079030

- 27-piece 3/8" ratchet set including fine-toothed Zyklop Speed ratchet with swivelling ratchet head, push-button release and right/left switching
- Low return angle of only 5° for working in a small space
- Long bit sockets with extra slim, cylindrical profile zone for low-located couplings (e.g. for bottom bracket ball bearing or stem-fork-clamping)
- 8790 HMB Deep socket wrench insert size 15 for use in cap socket couplings
- Sockets and bits for the most popular screw profiles for road bikes, mountain bikes and e-bikes
- Assortment in robust textile box with low weight for easy transport
- With adapter from 3/8" square head socket to 1/2" external square head for mounting special bicycle tools

27-piece 3/8" ratchet set for typical bicycle operations with extensive accessories:

1 Zyklop Speed ratchet with 3/8" drive, 10 Zyklop sockets, 2 Zyklop bit sockets with 30mm and extra slim profile area for better accessibility in tight workspaces. With Take it easy tool finder: Colour coding by size. 1 Zyklop extension (short) with fast-rotating sleeve, 1 Wobble extension, 1 bit adapter, 1 connection part 3/8" external square head to 1/2" external square head, 10 bits, tough, for universal use. Incredibly compact set arrangement for many tools in a tight space thanks to the highly robust and durable textile box. Can be placed in an upright position for clearly arranged storage in the workshop shelf. Additional surface protection due to textile outer material. Low weight and small size for better mobility.



Web link

https://products.wera.de/en/ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_3_8_the_zyklop_speed_ratchet_3_8_bicycle_set_7.html

Wera - Bicycle Set 7
05004175001 - 4013288220608

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Zyklop "6 in 1"



1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

Pivots freely




The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

Fast movers



The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

Simple direction change




All Zyklop Speed ratchets feature a thumbwheel that can be used to quickly and easily switch between clockwise and anticlockwise rotation, at any position. No complicated handling, no loss of time!

Low return angle



The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

30mm long and extra slim profile area



The bit sockets have a 30mm long and extra slim profile area. This makes even couplings in tight work spaces easily accessible.

The Zyklop sockets



The Zyklop sockets are suitable for manual and machine-operated tools (non impact). They feature a ball stop groove and knurling at the rear end for manageability during manual use. They are made of chrome-vanadium, dull chromed. Take it easy tool finder: Colour coding by size as well as size stamping - to help you find the required socket quickly and easily.

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Web link

https://products.wera.de/en/ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_3_8_the_zyklop_speed_ratchet_3_8_bicycle_set_7.html

Wera - Bicycle Set 7
05004175001 - 4013288220608

Wera Werkzeuge GmbH
Körzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bicycle Set 7, 27 pieces

The Zyklop Speed Ratchet, 3/8"



Set contents:

8000 B Zyklop Speed Ratchet with 3/8" drive, 3/8" x 199 mm



05003550001

1x 3/8" x 199 mm



8790 HMB Zyklop 3/8" socket, 6 x 29 mm



05003551001

1x 6 x 29 mm

05003552001

1x 7 x 29 mm

05003553001

1x 8 x 29 mm

05003554001

1x 9 x 29 mm

05003555001

1x 10 x 29 mm

05003556001

1x 11 x 29 mm

05003557001

1x 12 x 29 mm

05003558001

1x 13 x 29 mm

05003559001

1x 14 x 29 mm



8790 HMB Deep 3/8" socket, 15 x 64 mm



05004537001

1x 15 x 64 mm



8740 B Zyklop Bit socket with 3/8" drive, with extra slim profile area, 8 x 100 mm



05003054001

1x 8 x 100 mm

05003056001

1x 10 x 100 mm



8794 B Zyklop wobble extension, 3/8", 3/8" x 76 mm



05003584001

1x 3/8" x 76 mm



8784 B1 Zyklop bit adaptor, 3/8", 1/4" x 3/8" x 44 mm



05003590001

1x 1/4" x 3/8" x 44 mm



8794 SB Zyklop extension with free-turning sleeve, short, 3/8", 3/8" x 125 mm



05003582001

1x 3/8" x 125 mm



781 B 3/8" Connection parts, 781 B/C x 1/2 x 36 mm x 3/8"



05042673001

1x 781 B/C x 1/2 x 36 mm x 3/8"



Web link

https://products.wera.de/en/ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_3_8_the_zyklop_speed_ratchet_3_8_bicycle_set_7.html

Wera - Bicycle Set 7

05004175001 - 4013288220608

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Bicycle Set 7, 27 pieces

The Zyklop Speed Ratchet, 3/8"



840/4 Z bits, 3 x 50 mm



05059605001
05059610001
05059615001
05059620001¹⁾

1) Hexagonal blade

1x 3 x 50 mm
1x 4 x 50 mm
1x 5 x 50 mm
1x 6 x 50 mm

867/4 Z TORX® bits, TX 10 x 50 mm



05060132001
05060133001
05060134001
05060135001
05060136001
05060137001

1x TX 10 x 50 mm
1x TX 15 x 50 mm
1x TX 20 x 50 mm
1x TX 25 x 50 mm
1x TX 27 x 50 mm
1x TX 30 x 50 mm

Web link

https://products.wera.de/en/ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_3_8_the_zyklop_speed_ratchet_3_8_bicycle_set_7.html

Wera - Bicycle Set 7

05004175001 - 4013288220608

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de