


Parts Information:

Compressor 150ltr Belt Drive 3hp with Cast Cylinders

Model No: SAC1153B



Item	Part No.	Description
1	SAC5010140008	BASE PLATE
2	SAC5157260008	TANK 150ltr
3	SS825.S	HEX HEAD SET SCREW M8x25mm SINGLE
4	SS1045.S	HEX HEAD SET SCREW M10x45mm SINGLE
5	SFS1020.S	HEX HEAD FLANGE BOLT M10x20 SINGLE
6	MSP512.S	MACHINE SCREW PAN HEAD PHILLIPS M5x12mm
7	SAC7012170000	SCREW (M5x8)
8	SN8.S	STEEL NUT M8 ZINC DIN934 (SINGLE)
9	SN10.S	STEEL NUT M10 ZINC DIN934(SINGLE)
10	FWM8.S	FLAT WASHER M8 SINGLE
11	RW625.S	REPAIR WASHER M6x25 (SINGLE)
12	RW619.S	REPAIR WASHER M6x19 (SINGLE)
13	SAC7080160000	ELBOW 1/2"
14	SAC7090030000	PLUG 1/2
15	SAC7130150000	TAP 1/2" M/F
16	SAC7130160000	TAP 3/8"
17	SAC7190090000	NON-RETURN VALVE

Item	Part No.	Description
18	SAC7192090000	SAFETY VALVE
19	SAC7230010000	RISLAN HOSE (SOLD PER 1 METER)
20	SAC7233711000	DELIVERY PIPE
21	SAC4170010000	BELT GUARD KIT
22	V/A47	V-BELT (ID-1200) A47
23	SAC1127380796	MOTOR (BLACK FAN COVER TWO CAPACITORS)
24	SAC7409570000	MOTOR PULLEY 160MM - SINGLE BELT
25	SAC7458510000	BELT GUARD SUPPORT
26	SAC9101880000	PUMP UNIT
40	SAC4057630000	PRESSURE SWITCH KIT 20Amp 15Bar 220Psi
41	SAC7023050000	LOCK NUT
42	SAC7088060000	CONNECTOR
43	SAC7090070000	PLUG 1/4"
44	SAC9700001789	PRESSURE GAUGE 230 psi, 50mm OD, rear fit
45	SAC7250360000	PRESSURE SWITCH 20Amp
46	SAC7329010000	POWER CABLE

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk






Parts Information:

Compressor 150ltr Belt Drive 3hp with Cast Cylinders

Model No: SAC1153B



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk



Parts Information:

Compressor 150ltr Belt Drive 3hp with Cast Cylinders

Model No: SAC1153B

1	SAC9700001075	CRANKCASE
2	SAC9700001076	CRANKCASE COVER
3	SAC9700000531	SCREW (M5x12)
4	SAC9700001077	CRANKCASE BASE SEAL
5	SAC9100270140	CRANKSHAFT
6	B/6203	BEARING 6203
7	B/6204	BEARING 6204
8	SAC9100270150	OIL SEAL
9	SAC9100270160	FRONT COVER
10	SAC9100270170	REAR COVER
11	SAC9100280010	O-RING 46.2x39.6x3.3 (FRONT COVER SEAL)
12	SAC7011420000	SCREW (M6x16)
13	SAC9100280020	KEY
14	SAC9100270010	CONNECTION ROD
15	SAC9100270020	GUDGEON PIN
16	SAC9100270030	PISTON
17	SAC4080120000	KIT OF PISTON RINGS
18	SAC9100270070	SEEGER RING (OGIVE)
19	SAC9100270080	CYLINDER(TWIN)
20	SAC7012220000	SCREW (SO)
21	SAC9100280070	OIL SIGHT GLASS
22	SAC9100270180	GASKET, CYLINDER BASE
23	SAC9100270190	GASKET
24	SAC9100270090	VALVE PLATE (CAST WITH HOLE FOR REEDS)
25	SAC9100270200	GASKET
26	SAC9100280090	VALVE

	B. J.N.	Barrier
Item	Part No.	Description
27	SAC9100270210	GASKET
28	SAC9100270100	CYLINDER HEAD
29	SAC7458340000	PLATE
30	SAC7210010000	FILTER ELEMENT
31	SAC9100270240	INTAKE FILTER
32	SAC7012100000	RD HEAD S/T SCREW M3.8 X 15
33	SCB855.S	SOCKET CAP BOLT ZINC M8X55
34	SAC9100270220	COVER
35	MSP512.S	MACHINE SCREW PAN HEAD PHILLIPS
		M5x12mm
36	SS616.S	HEX HEAD SET SCREW M6x16mm SINGLE
37	SAC9100280110	BREATHER PLUG
38	RW825.S	REPAIR WASHER M8x25 (SINGLE)
39	SAC9100270230	FLYWHEEL
40	SS825.S	HEX HEAD SET SCREW M8x25mm SINGLE
41	SAC7031010000	TOOTHED WASHER
42	SAC9100270270	AFTERCOOLER
43	FWM8.S	FLAT WASHER M8 SINGLE
44	SAC9100270280	GASKET
45	SAC7080160000	ELBOW 1/2"
46	SAC9700000693	PLUG 3/8"
100	SAC9700003272	VALVE PLATE ASS'Y
101	SAC9700000078	GASKET KIT
102	SAC9700010170	PISTON GROUP

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

01284 757500



01284 703534



sales@sealey.co.uk

