# SEALEY

## INSTRUCTIONS FOR

# TROLLEY 2/3 LEVEL HEAVY-DUTY

MODEL NO: **CX102.V2 & CX103.V2** 

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.



Refer to instructions

# 1. SAFETY

#### 1.1. GENERAL SAFETY

- □ WARNING! Ensure Health & Safety, local authority, and general workshop practice regulations are adhered to when using this trolley.
- ✓ Always load evenly with the centre of gravity of the load as near centre of the trolley as possible.
- **DO NOT** overload the trolley see Specifications section 3.
- ✓ Use the trolley in a suitable work area.
- ✓ Keep the work area clean, uncluttered and ensure there is adequate lighting.
- ✓ Keep the trolley clean and tidy in accordance with good workshop practice.
- f x DO NOT use the trolley for any purpose other than that for which it is designed.
- DO NOT stand on the trolley, use it as a ladder or allow others to ride on the trolley.
- ✓ Use the wheel locks to prevent the trolley from inadvertently moving.
- DO NOT leave unattended, especially when loaded, unless the wheels are locked, chocked or the trolley otherwise secured.
- DO NOT use trolley on uneven ground and do not run over curbs or steps use a ramp.
- **DO NOT** use trolley if any part is significantly damaged, paying particular attention to the wheels.
- Keep children and unauthorised persons away from the work area.

# 2. INTRODUCTION

Garage or workshop trolley with a 75kg (CX103.V2 50kg) capacity per shelf. Deep-walled shelves, which may be installed base down or base up to give either tool or component security or unobstructed access. Fitted with four wheels, two fixed and two locking castors.

## 3. SPECIFICATION

Model no's:	CX102.V2/CX103.V2
Overall size (W x D x H):	775 x 410 x 900mm
Capacity total kg:	
CX102.V2:	150kg (75kg/level)
CX103 V2·	150kg (50kg/level)

# 4. ASSEMBLY

- 4.1. Mount shelf to the upper hole in the end columns and loosely fix with M8 x 35mm screws and nuts.
- 4.2. Mount the other 2 (CX102.V2) or 3 (CX103.V2) shelves and loosely fix with M8 x 35mm screws and nuts.
- 4.3. Turn trolley over install castors into the bottom of the end frames, use 16mm spanner. Ensure two locking castors are fixed to same end.
- 4.4. Tighten all fixings.
- 4.5. Turn the trolley upright, it is now ready to use.





Parts support is available for this product. To obtain a parts listing and/or diagram, please log on to www.sealey.co.uk, email sales@sealey.co.uk or telephone 01284 757500



# **ENVIRONMENT PROTECTION**

Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain any fluids (if applicable) into approved containers and dispose of the product and fluids according to local regulations.

**Note**: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

Important: No Liability is accepted for incorrect use of this product.

Warranty: Guarantee is 12 months from purchase date, proof of which is required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR

1 01284 757500 01284 703534 sales@sealey.co.uk www.sealey.co.uk