



EAN:	4013288234858	Size:	270x60x50 mm
Part number:	05135882001	Weight:	744 g
Article number:	8000 C Black Edition	Country of origin:	CZ
		Customs tariff number:	82041100

- Premium and robust matte-black chrome-plated surface
- Combines five different types of a ratchet in one
- Flywheel design and easy-to-grip free-turning sleeve for very high working speeds
- Freely pivoting ratchet head, push button release and left/right switchover
- Fine-tooth design allows a small return angle of 5°
- Can also be used as a screwdriver

Zyklop ratchet with 1/2" drive. Premium and robust matte-black chrome-plated surface. The fine toothing with 72 teeth allows for a low return angle of 5°. The ratchet head swivels freely and can be locked in any position using the slide switch on both sides. Unproblematic working with plenty of hand space even in very narrow or difficult-to-reach installation situations. The pre-defined positions at 0°, 15° and 90° to the left and right guarantee safe working without the ratchet head slipping. In the 0° position, the ratchet with adapter and bit can be used like a conventional screwdriver. The flywheel design helps accelerate the screwdriving process. The rotationally symmetrical design of the Kraftform handle and the fast-rotating sleeve support rapid turning. Thanks to the shape of the Kraftform handle being perfectly adapted to the hand, hand injuries such as blisters and calluses are avoided. The hard materials used for the handle guarantee quick hand switching without the risk of the skin "sticking" to the handle. The softer, "non-slip" zones offer transmission of high forces without loss. For 1/2" square head sockets as well as 1/2" connectors with square head drive, with ball lock.



Web link

https://products.wera.de/en/new_products_2025_tools_black_edition_limited_edition_zyklop_speed_black_edition_ratchet_8000_c_black_edition.html

Wera - 8000 C Black Edition
 05135882001 - 4013288234858

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Zyklop "6 in 1"



1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

Pivots freely



The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

Fast movers



The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

Simple direction change



All Zyklop Speed ratchets feature a thumbwheel that can be used to quickly and easily switch between clockwise and anticlockwise rotation, at any position. No complicated handling, no loss of time!

Low return angle




The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

Can also be used as a screwdriver



The ratchet can be used as a conventional screwdriver in the 0° position by attaching a bitholding adaptor and a bit.

Ball lock



The ball lock holds the sockets and attachments securely, ensuring safe working. A changeover into any predefined position is completed by simply pressing the release button - this is even the case in the 90° position.

Multicomponent Kraftform handle



The outstanding design of the Kraftform handle fits perfectly into the hand, preventing hand injuries such as blisters and calluses. The hard materials used for the handle ensure quick and easy hand repositioning without any danger of the skin "sticking" to the handle, whilst the softer "anti-slip" zones enable the low-loss transfer of high forces - resulting in less screwdriving effort being required. The circular handle design allows rapid turning in the 0° position.

Web link

https://products.wera.de/en/new_products_2025_tools_black_edition_limited_edition_zyklop_speed_black_edition_ratchet_8000_c_black_edition.html

Wera - 8000 C Black Edition
05135882001 - 4013288234858

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Zyklop Speed Black Edition ratchet

Further versions in this product family:



inch



mm

05135882001	1/2"	277.0
-------------	------	-------

Web link

https://products.wera.de/en/new_products_2025_tools_black_edition__limited_edition_zyklop_speed_black_edition_ratchet_8000_c_black_edition.html

Wera - 8000 C Black Edition
05135882001 - 4013288234858

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de