



Article number: Tool-Check 1

Country of origin: CZ


Customs tariff number: 82079030

- Very compact 38-piece tool set for manual and machine use
- Perfect for a wide variety of screw connections with Zyklop Mini with 1/4" bit mounting and/or bitholding screwdriver
- Green locking components to secure the tools
- Ideal for mobile use
- 1/4" bit ratchet, tough (Z) and hard (H) bits, Rapidaptor bit holder, adapter and 1/4" sockets
- Bits with Torsion design (T) preventing premature wear
- Use of 1/4" sockets also possible with the Wera adaptor 870/1
- Sockets with Take it easy tool finder: colour coding by size and size stamping

38-piece set. Very compact tool set for manual and machine use. The green locking elements of the Tool-Check secure the tools during transport. Includes one 1/4" bit ratchet in drop-forged solid steel design. Fine toothing mechanism (60 teeth) for a small return angle of 6° for precise working. Easy clockwise/counterclockwise switching. Ergonomically shaped ratchet head and lever. 1/4" sockets can also be used with the Wera 870/1 adapter (1/4" external hexagon to 1/4" external square head) included in the set. 7 Zyklop sockets (1/4", for manual and machine-operated tools); with ball stop groove. Knurling at the rear end for manageability during manual screwdriving. With Take it easy tool finder: colour coding by size - for quick and easy identification of the required tool. Made of matt chrome-plated chrome-vanadium. 28 tough bits (Phillips and Pozidriv, TORX®, TORX® B0, slotted and hexagonal socket) for universal use. In the very compact, functional Tool-Check.



Compact Tool-Check



Zyklop Mini



The set offers 38 tools in an extremely space-saving box. The Tool-Check is made of premium plastic, guarantees neat arrangement, quick access to the required tools and secure transport - no risk of losing tools!

Safely stored



The green locking components of the Tool-Check secure the tool reliably during transport. At the same time, they are easy to operate and allow quick access to the tools.

Ideal for working in confined spaces



With their extremely compact design, the Zyklop Mini ratchets are particularly suitable for all hard-to-reach applications.

High power transmission



The Zyklop Mini ratchet can withstand at least 65 Nm, which is far more power than you can normally transfer to such a small tool.

The Zyklop Mini




The fine tooth mechanism, with its 60 teeth, allows a small return angle of only 6° - ideal for precision work.

Reversible clockwise/counterclockwise



With the ergonomically placed reversing lever, the bit ratchet can be easily switched from clockwise to counterclockwise screwdriving.

Rapid screwdriving



High working speeds can be attained with the Zyklop Mini bit ratchet. The thumb wheel is important, enabling more rapid screwdriving, and the lever of the Zyklop Mini only needs to be used for the final tightening of the screw.

Web link

https://products.wera.de/en/new_products_2025_tool-check_modular_tool-check_plus_tool-check_tool-check_plus_tool-check_tool-check_1.html

Wera - Tool-Check 1
05049050001 - 4013288234889

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Tool-Check 1, 38 pieces

Tool-Check PLUS, Tool-Check



Set contents:

8001 A Bit Ratchet 1/4", 1/4" x 87 mm



1x 1/4" x 87 mm



889/4/1 K Rapidaptor Universal Bit Holder, 1/4" x 50 mm



05052502001

1x 1/4" x 50 mm



870/1 Adaptor, 1/4" x 25 mm



05136000001¹⁾

1x 1/4" x 25 mm



1) With friction ball; for manual nut spinner sockets

851/1 TZ bits, PH 1 x 25 mm



05056505001

2x PH 1 x 25 mm

05056510001

3x PH 2 x 25 mm

05056525001

1x PH 3 x 25 mm



Web link

https://products.wera.de/en/new_products_2025_tool-check_modular_tool-check_plus_tool-check_tool-check_plus_tool-check_tool-check_1.html

Wera - Tool-Check 1

05049050001 - 4013288234889

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Tool-Check 1, 38 pieces

Tool-Check PLUS, Tool-Check



855/1 TH bits, PZ 1 x 25 mm



05056910001	1x	PZ 1 x 25 mm
05056915001	3x	PZ 2 x 25 mm
05056925001	1x	PZ 3 x 25 mm

867/1 TZ TORX® bits, TX 10 x 25 mm



05066305001	1x	TX 10 x 25 mm
05066308001	1x	TX 15 x 25 mm
05066310001	1x	TX 20 x 25 mm
05066312001	1x	TX 25 x 25 mm
05066315001	1x	TX 30 x 25 mm
05066320001	1x	TX 40 x 25 mm

867/1 Z TORX® B0 bits with bore hole, TX 10 x 25 mm



05066500001	1x	TX 10 x 25 mm
05066505001	1x	TX 15 x 25 mm
05066510001	1x	TX 20 x 25 mm
05066515001	1x	TX 25 x 25 mm
05066525001	1x	TX 30 x 25 mm

800/1 TZ bits, 1 x 5.5 x 25 mm



05056225001	1x	1 x 5.5 x 25 mm
-------------	----	-----------------

840/1 Z bits, 3 x 25 mm



05056315001	1x	3 x 25 mm
05056320001	1x	4 x 25 mm
05056325001	1x	5 x 25 mm
05056330001	1x	6 x 25 mm
05056335001	1x	8 x 25 mm

8790 HMA Zyklus 1/4" socket, 5.5 x 23 mm



05003504001	1x	5.5 x 23 mm
05003505001	1x	6 x 23 mm
05003506001	1x	7 x 23 mm
05003507001	1x	8 x 23 mm
05003509001	1x	10 x 23 mm
05003511001	1x	12 x 23 mm
05003512001	1x	13 x 23 mm

Web link

https://products.wera.de/en/new_products_2025_tool-check_modular_tool-check_plus_tool-check_tool-check_plus_tool-check_tool-check_1.html

Wera - Tool-Check 1

05049050001 - 4013288234889

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de